



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

COVER REMOVED FOR CLARITY



PAN-TY LOOPS
FOR CABLE HOLD-DOWNS


POST FOR TAMPER
RESISTANT SCREW



3.62

[92.0]

BREAKOUT AREA
(3 PLACES)



3.31

[84.0]

.94

[24.0]

PANDUIT P/N

WEIGHT


JOS35800Y
JOS35800BL

1.73 LB/10 PCS
(784.7 g/10 PCS)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN [] ARE IN METRIC.
4. BREAKOUTS DESIGNED TO ACCEPT LD3/LDP3 AND LD5/LDP5 RACEWAY.
5. BOX INCLUDES:
 - 1- BOX BASE
 - 1- BOX COVER
 - 2- PLT1.51-M PAN-TY
 - 1- LABEL/ LABEL COVER
 - 1- MOUNTING SCREW (USED TO SECURE COVER TO BASE)
 - 2- MAGNET (ATTACHED) (CSBM-X)
 - 3- MINI-COM MINI-JACK CATEGORY 5e MODULE
6. BASE MATERIAL THICKNESS= .090 [2.29]

LABEL HOLDER/ SECURITY
SCREW PLACEMENT



PART NUMBER

JOS35800Y, JOS35800BL

TITLE

MINI-COM 3 POSITION SHUTTERED SURFACE MOUNT
BOX KIT

CUSTOMER DRAWING

ITEM REVISION NAME

M02479BW/00

DATASET FILE NAME

M02479BW_DC049/00D


UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE: IN [mm]

.X ±

.XX ± .03 [.8]

.XXX ± .010 [.3]

ANGLES ±



THIRD ANGLE
PROJECTION

MATERIAL:

BOX: ABS
DOORS: PC

DRAWING NUMBER:

02479-049

DRAWN BY

JSP

DATE

3-26-07

CHK

MJD

SCALE

NONE

SHT 1 OF 1

SIZE

A

REVISED AND REDRAWN, PREVIOUS REVISIONS
HAVE BEEN OMITTED.

02479-049

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
3	5/30/14	JSP	REFR	MMR	REVISED AND REDRAWN, PREVIOUS REVISIONS HAVE BEEN OMITTED.	02479-049