

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
P36B###M-XXYZ	SEE SHEET 2

SPECIFICATION:

- | | |
|---|---|
| 1. STANDARD UNIT TYPE:
ORIENTATION:
OUTLET QTY & TYPE:
INPUT VOLTAGE:
INPUT CURRENT:
BREAKER QTY & TYPE:
INPUT PHASE:
RATED POWER:
INPUT PLUG:
INPUT POWER CORD: | BASIC
VERTICAL, 0U FULL
SEE SHEET 2 FOR CONFIGURATIONS
200-240/346-415VAC
30A (24A DERATED)
(6) 20A, SINGLE POLE
THREE-PHASE WYE
17.3 kVA
SEE SHEET 2 FOR CONFIGURATIONS
SEE SHEET 2 FOR PART NUMBER TABLE |
|---|---|

REGULATORY STANDARD: RoHS COMPLIANT

2. ADDITIONAL:
CIRCUIT BREAKERS RATED AT 10KAIC


3. ACCESSORIES:
(1) QUICK-START GUIDE

NOTES:


- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSIONS ARE IN [INCHES]
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PRODUCT
- FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
- DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

IDENTIFICATION


FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: **P36B###M - XYZ**




BOTTOM VIEW



FOUR CHARACTER SUFFIX FOR ALTERNATE PRODUCT CONFIGURATIONS



LEFT VIEW



REAR VIEW


TOOLESS MOUNTING
BUTTON LOCATIONS (12)PL



RIGHT VIEW

20A, SINGLE-POLE
ELECTRO MECHANICAL
SWITCH / BREAKER (6)PL

SEE SHEET 2 FOR LOAD BANK DESIGNATIONS



FRONT VIEW

PLUG/ RECEPTACLE BLOCK

	IEC 60309, 4P 5W, 6H IP67 (WATERTIGHT) 30A, 346-415V MAX RATED INPUT 24A DERATED		IEC 60320/C19 16A, 250V MAX RATED OUTPUT
	IEC 60309, 4P 5W, 6H IP44 (SPASHPROOF) 30A, 346-415V MAX RATED INPUT 24A DERATED		IEC 60320/C13 10A, 250V MAX RATED OUTPUT
	NEMA L22-30P, 4P 5W 30A, 277-480V MAX RATED INPUT 24A DERATED		

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGNTHE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.

TITLE INTELLIGENT SERIES PDU P36B###M-XXYZ		SIGN	
ITEM REVISION NAME		DATE	
DATASET FILE NAME		PRINT	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: mm [IN]		MATERIAL:	
Tolerance (mm)		DRAWING NUMBER: P36B_DC	
THRID ANGLE PROJECTION		SHEET 1 OF 2	
BY WAC	DATE 03/14/19	CHK -	SCALE NTS


REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
01A	3/21/2019	WAC	DACU	JAWI	RELEASED TO PRODUCTION	P36B

D10100DB/17

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	INPUT PLUG CONFIGURATION	RECEPTACLE CONFIGURATION	COLOR	INPUT CORD LENGTH	WEIGHT
P36B02M	VERTICAL, (24)C13, (12)C19, BASIC, 200-240/346-415V/ 30A/3 PHASE WYE, TOP-END FED, 3 METER INPUT CORD, BLACK	L22-30P 30A 4P, 5W	(24) C13, (12) C19	BLACK (RAL 9005)	3M(+254MM/-127MM) 10' [+10"/-5"]	6.9kg
P36B01M	VERTICAL, (24)C13, (12)C19, BASIC, 200-240/346-415V/ 30A/3 PHASE WYE, TOP-END FED, 3 METER INPUT CORD, BLACK	IEC60309 30A 4P, 5W, IP67 (WATERTIGHT)	(24) C13, (12) C19	BLACK (RAL 9005)	3M(+254MM/-127MM) 10' [+10"/-5"]	6.9kg
P36B03M	VERTICAL, (24)C13, (12)C19, BASIC, 200-240/346-415V/ 30A/3 PHASE WYE, TOP-END FED, 3 METER INPUT CORD, BLACK	IEC60309 30A 4P, 5W, IP44 (SPASHPROOF)	(24) C13, (12) C19	BLACK (RAL 9005)	3M(+254MM/-127MM) 10' [+10"/-5"]	6.9kg

(24)C13, (12)C19



WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.

SIGN _____
DATE _____
PRINT _____

TITLE
INTELLIGENT SERIES PDU
P36B##M-XXYZ
CUSTOMER DRAWING

ITEM REVISION NAME _____
DATASET FILE NAME _____

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: mm [IN]

Tolerance (mm)
0<L<50 ±0.5
50<L<250 ±1.0
250<L<500 ±1.5
500<L<1000 ±2.5
1000<L<2000 ±4.0

MATERIAL: _____
DRAWING NUMBER: **P36B_DC**

BY: WAC DATE: 03/14/2019 CHK: - SCALE: NTS
SHEET 2 OF 2 SIZE: B

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
01A	3/21/2019	WAC	DACU	JAWI	RELEASED TO PRODUCTION	P36B

D:\01\00DB\17