


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

TWIST TIES



T568B WIRING SCHEME

PLUG POSITION:

1
2
3
4
5
6
7
8

CABLE WIRE:
WHITE/ORANGE
ORANGE
WHITE/GREEN
BLUE
WHITE/BLUE
GREEN
WHITE/BROWN
BROWN

NOTES:

1. TX6A 10GIG PLUG-TO-JACK ZONE CORD
2. 100% PERFORMANCE TESTED TO CATEGORY 6A PERMANENT LINK LIMITS
3. TERMINATED AT ONE END WITH (8 POSITION) RJ45 MODULAR PLUG PER T568B AND AT OTHER END WITH TX6A 10GIG JACK
4. CONSTRUCTED WITH 23AWG SOLID CATEGORY 6A STP LOW SMOKE ZERO HALOGEN, PLENUM, OR RISER CABLE.
5. MATERIALS:
PLUG: POLYCARBONATE
BOOT: BLACK PVC
JACK HOUSING: ABS
JACK SHIELD: TIN PLATED OVER PHOS. BRONZE
WIRE CAP/CLIP: ZINC AND PC
PLUG SHIELD: COPPER ALLOY NICKEL PLATED






FIGURE 2

SEE SHEET 2 FOR ZONE CORD
LENGTHS AND PART NUMBERS

PART NUMBER SAJ* SERIES		PRODUCT SPEC/PKG SPEC N/A	
I.I. NUMBER N/A		WORK INSTRUCTION N/A	
TITLE TX6A 10GIG SHIELDED PLUG-TO-JACK ZONE CORD			
CUSTOMER DRAWING			
ITEM REVISION NAME M02678BI-DC09_00A/AA			
DATASET FILE NAME M02678BI-DC09/00F			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °		MATERIAL: SEE NOTES	
		DRAWING NUMBER: 02678-09	
DRAWN BY BJN	DATE 3-5-08	CHK RJDU	SCALE NONE
		SHT 1 OF 2	
		SIZE A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
5	12-17-13	BJN	EJH	EJH	UPDATED	02678-09

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

10GIG STP PLUG-TO-PLUG ZONE CORDS


LSZH	CMP	CMR
PART NUMBERS	PART NUMBERS	PART NUMBERS
SAJLWH**MBL	SAJPBU**	SAJRBU**
MIN. CABLE LENGTH	MIN. CABLE LENGTH	MIN. CABLE LENGTH
4 METERS (158")	10 FEET (120")	10 FEET (120")
5 METERS (197")	15 FEET (180")	15 FEET (180")
6 METERS (237")	20 FEET (240")	20 FEET (240")
7 METERS (276")	25 FEET (300")	25 FEET (300")
8 METERS (315")	30 FEET (360")	30 FEET (360")
9 METERS (355")	35 FEET (420")	35 FEET (420")
10 METERS (394")	40 FEET (480")	40 FEET (480")
11 METERS (434")	45 FEET (540")	45 FEET (540")
12 METERS (473")	50 FEET (600")	50 FEET (600")
13 METERS (512")	55 FEET (660")	55 FEET (660")
14 METERS (552")	60 FEET (720")	60 FEET (720")
15 METERS (591")	65 FEET (780")	65 FEET (780")
16 METERS (630")	70 FEET (840")	70 FEET (840")
18 METERS (709")	75 FEET (900")	75 FEET (900")
20 METERS (788")	80 FEET (960")	80 FEET (960")
22 METERS (867")	85 FEET (1020")	85 FEET (1020")
24 METERS (945")	90 FEET (1080")	90 FEET (1080")
26 METERS (1024")	95 FEET (1140")	95 FEET (1140")
28 METERS (1103")	100 FEET (1200")	100 FEET (1200")
30 METERS (1182")	110 FEET (1320")	110 FEET (1320")
32 METERS (1260")	120 FEET (1440")	120 FEET (1440")
34 METERS (1339")	130 FEET (1560")	130 FEET (1560")
36 METERS (1418")	140 FEET (1680")	140 FEET (1680")
38 METERS (1497")	150 FEET (1800")	150 FEET (1800")
40 METERS (1575")		
42 METERS (1654")		
44 METERS (1733")		
46 METERS (1812")		
48 METERS (1890")		
50 METERS (1969")		

LSZH OFFERED WITH WHITE CABLE. (METERS ONLY)

CMP & CMR OFFERED WITH BLUE CABLE.
(FEET ONLY)

STRAIN RELIEF BOOTS AVAILABLE IN
BLACK ONLY.

**=LENGTH (SEE FIGURE 2, SHEET 1)

PART NUMBER SAJ* SERIES		PRODUCT SPEC/PKG SPEC N/A	
I.I. NUMBER N/A		WORK INSTRUCTION N/A	
TITLE TX6A 10GIG SHIELDED PLUG-TO-JACK ZONE CORD			
CUSTOMER DRAWING			
ITEM REVISION NAME M02678BI-DC09-00A/AA		PANDUIT	
DATASET FILE NAME M02678BI-DC09/00F			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °		MATERIAL: SEE NOTES	
THIRD ANGLE PROJECTION 		DRAWING NUMBER: 02678-09	
DRAWN BY BJN	DATE 3-5-08	CHK RJDU	SCALE NONE
SHT 2 OF 2			SIZE A

5	12-17-13	BJN	EJH	EJH	SEE SHEET 1 FOR REVISION HISTORY	02678-09
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN