


SmartZone[™] G5 iPDUs

Featuring Combination Outlets for Higher Outlet Density and Increased Power Capacity

Digitization has created the need to maximize IT equipment in the rack.

The G5 iPDU 4-in-1 combination outlets provide the ultimate in connection flexibility allowing a single receptacle to be used as a C13/C15 or a C13/C15/C19/C21, making sure connection types are available when needed most. The 4-in-1 combination outlets accept Panduit dual-locking power cords eliminating accidental disconnects. The G5 PDUs also feature higher power capacities than ever before, allowing more equipment to be powered from a single PDU. Available in Monitored Input (MI), Monitored Switched (MS), or Monitored & Switched per Outlet (MSPO) varieties with power capacities ranging from 8.6KW to 43.5KW.



Power Distribution Units

Part Number	Voltage & Phase	Input Current per Phase	Input Plug	Form Factor	Circuit Breakers	Outlet Count	Outlet Configuration	Length
Monitored Inp	ut – MI Series							
P48D20M	230/415VAC, 3-Phase	30A/32A	IEC 60309 3P+N+E 6h 30A/32A (IP44)	OU FULL OU MID	6	48	(24)C13, C15, (24)C13, C15, C19, C21	70"
P48D23M		20A/16A	IEC 60309 3P+N+E 6h 20A/16A (IP44)		_			58.6"
P42D21M		60A/63A	IEC 60309 3P+N+E 6h 60/63 (IP44)	OU FULL	12	42	(21)C13, C15, (21)C13, C15, C19, C21	72"
P48D21M	208VAC, 3-Phase	30A	NEMA L21-30P		3		(24)C13, C15, (24)C13, C15, C19, C21	70"
P48D22M			L15-30P					
P42D20M		60A/63A	IEC 60309 3P+E 9h 60A (IP44)		6	48		
P42D22M		50A	CS8365					
Monitored Sw	itched – MS Series							
P48E20M	230/415VAC, 3-Phase	30A/32A	IEC 60309 3P+N+E 6h 30A/32A (IP44)	OU FULL	6	48	(24)C13, C15, (24)C13, C15, C19, C21	70"
P48E23M		20A/16A	IEC 60309 3P+N+E 6h		_			58.6"
P48E25M		60A/63A	EC 60309 3P+N+E 6h 60/63A (IP44)		12			70"
P48E21M	208VAC, 3-Phase	30A	NEMA L21-30P		3			
P48E22M			L15-30P					
P48E24M		60A	IEC 60309 3P+E 9h 60A (IP44)		6			
P48E26M		50A	CS8365					
Monitored Sw	itched Per Outlet –	MSP0 Series						
P48G30M	230/415VAC, 3-Phase	30A/32A	IEC 60309 3P+N+E 6h 30A/32A (IP44)	OU FULL	6	48	(24)C13, C15, (24)C13, C15, C19, C21	70"
P48G33M		20A/16A	IEC 60309 3P+N+E 6h 20A/16A (IP44)		_			58.6"
P42G21M		60A/63A	IEC 60309 3P+N+E 6h 60A/63A (IP44)		12	42	(21)C13, C15, (21)C13, C15, C19, C21	71.9"
P48G31M	208VAC, 3-Phase	30A	NEMA L21-30P		3	48	(24)C13, C15, (24)C13, C15, C19, C21	70"
P48G32M			L15-30P					
P42G20M		60A	IEC 60309 3P+E 9h 60A (IP44)		6			
P42G22M		50A	CS8365			24	(21)C13, C15, (21)C13, C15, C19, C21	
Monitored Pe	Outlet – MPO Seri	es		'				
			Dil+ +	o Order				

Related Products

Part Number	Description					
Environmental Sensors						
EA001	Temperature Environmental Sensor					
EB001	Temperature and Humidity Sensor					
EC001	3 Temperature and Humidity Sensor					
ED001	Water Sensor Rope Type					
Locking Power Cord	ls					
LPCA12-X	4FT, Black, 17 AWG, 10A/250V, Locking Power Cord, IEC C14 to IEC C13, 10 Pack					
LPCA14-X	8FT, Black, 17AWG, 10A/250V, Locking Power Cord, IEC C14 to IEC C13, 10 Pack					
LPCB12-X	4FT, Black, 15 AWG, 16A/250V, Locking Power Cord, IEC C20 to IEC C19, 10 Pack					
LPCB14-X	8FT, Black, 15AWG, 16A\250V, Locking Power Cord, IEC C20 to IEC C19, 10 Pack					

Part Number	Description				
Racks & Enclosures					
R2P	2 Post Rack, 45RU, #12-24 Threaded E-Rails, Aluminum, Black				
ARP4	4 Post Rack, Adjustable Depth, 45RU, #12-24 Threaded E-Rails, Black				
XG84522BS0005	FlexFusion Cabinet, 800mm x 45RU x 1200mm, Black				
N8212B	Net-Access™ N-Type Cabinet, 42 RU, Black, 800mm Wide				
Asset Management	& Monitoring				
SZC-PEIA1Y/3Y	Power & enviornmental infrastructure asset, 1-year or 3-year subscriptions				
SZC-ITIA1Y/3Y	IT infrastructure asset, 1-year or 3-year subscriptions				

To learn more about SmartZone G5 iPDUs, scan the QR code.



