# **NetKey® Category 5e UTP Patch Cords**



# **SPECIFICATIONS**

Category 5e/Class D patch cords shall be constructed of UTP 24 AWG stranded copper cable and a modular plug at each end. Patch cords shall be used in all work area outlets and patch panels. Patch cords shall be wired to be compatible with both T568A and T568B wiring schemes.



### **TECHNICAL INFORMATION**

Category 5e/Class D performance:	Exceeds ANSI/TIA-568-C.2 Category 5e and ISO 11801 Class D channel requirements at swept frequencies up to 100 MHz Meets ANSI/TIA-568-C.2 and ISO 11801 Category 5e component requirements at swept frequencies up to 100 MHz
FCC compliance:	Complies with ANSI/TIA-1096A (formerly FCC Part 68); contacts plated with 50 microinches of gold
IEC compliance:	Meets IEC 60603-7
PoE compliance:	Supports IEEE 802.3af/802.3at and proposed 802.3bt type 3 and type 4 PoE applications
c(UL)us compliance:	UL 1863 and CAN/CSA-C22.2 (UL File E129886)
RoHS compliance:	Compliant
Cable diameter:	0.215 in. (5.5mm) nominal
Flame rating:	CM rated

### **KEY FEATURES AND BENEFITS**

100% Performance tested:	Confidence that each patch cord delivers specified performance
Patented tangle-free latch:	Prevents snags and provides easy release
Identification:	Provides identification of performance level, length, and quality control number for future traceability
Variety of colors and lengths available:	Meets individual length and color-coding requirements

# **APPLICATIONS**

Applications include:

- Ethernet 10BASE-T, 100BASE-T (Fast Ethernet), and 1000BASE-T (Gigabit Ethernet)
- 155 Mb/s ATM, 622 Mb/s ATM, 1.2 Gb/s ATM
- Token Ring 4/16
- Voice over internet protocol (VoIP)

#### TX6 PLUS UTP Patch Cords

NK5EPC\*^Y Foot lengths: Meter lengths: NK5EPC\*\*M^Y

#### NetKey Category 5e Jack Moduless

NK5E88M^^Y Leadframe module:

Convenience pack of 25 leadframe modules:

NK5E88M^^Y

Punchdown module:

NKP5E88M^^

Convenience pack of 25 punchdown modules:

NKP5E88M^^-Q

\*Feet lengths: 3, 5, 7, or 10 feet

\*\*Meter lengths: 1, 2, 3, or 5 meters

^Colors other than Off White: BU (Blue), GR

(Green), or YL (Yellow)


A^Colors: IW (Off White), EI (Electric Ivory), IG (International Gray), WH (White), BL (Black), OR (Orange), RD (Red), BU (Blue), GR (Green), or YL (Yellow)

-Q indicates bulk packages with 25 pieces per pack to reduce singe-use plastic



# **NetKey® Category 5e UTP Patch Cords**

## **ENGINEERING DRAWINGS**





All Part Numbers Compliant with the U.S. Trade Agreements Act (TAA) for purchases shipped to the United States.

Dimensions are in inches. [Dimensions in brackets are metric].

#### **WORLDWIDE SUBSIDIARIES AND SALES OFFICES**

PANDUIT US/CANADA Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty



For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com

or by phone: 800.777.3300