


## THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

Material	High Conductivity Seamless Copper Tube		
Plating	Electro-Tin		
Wire Size	4/0 AWG		
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric		
Wire Strip Length	1-5/8 in.		
Stud Size	3/8 in.		
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.		
UL Temperature Rating	90° C		
C.S.A Certified Wire Connector	Yes		
Panduit Color Code on Barrel	PURPLE		
Panduit Die Index No. on Barrel	P54		
Alternate Industry Die Index No. ( ) on Barrel	(15)		











LISTED Wire Connector

						CORP. TINLEY PARK, ILLINOIS
						LCB4/0-38WF-X Copper Lug - One-Hole, Long Barrel with Window, 90° Angle Tongue
00	4/17	JHNU	JHNU	DRAWING RELEASED	021775	
REV	DATE	BY	СНК	DESCRIPTION	ECN	DRAWING NO / CAD FILE LCB4/0-38WF-CUST