


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AND TO INDICATE PACKAGE QUANTITY.
2. PATCH CORDS CAN BE USED WITH GP6 PLUS FOUR-PAIR CONNECTING BLOCKS.
3. THE GP6 PLUS PATCH CORD IS POLARIZED TO PREVENT REVERSE INSTALLATION TO THE CONNECTOR BLOCK, INCORPORATES A CABLE JACKET RETENTION FEATURE WHICH MINIMIZES WIRE UNTWISTING, AND HAS AN INTEGRAL STRAIN RELIEF.
4. PATCH CORDS CONSTRUCTED USING UL OR ETL VERIFIED CABLE.
5. MATERIAL:

CONNECTOR: POLYCARBONATE
 CABLE: CAT6, 24 AWG STRANDED-TIN/COPPER
 JACKET: PVC
 JACKET COLOR: WHITE

PANDUIT P/N	LENGTH (MIN) FEET (mm)	WEIGHT
GPPC4IG3Y	3 FT. (914mm)	1.17 LB/10 PCS (530 g/10 PCS)
GPPC4IG5Y	5 FT. (1524mm)	1.70 LB/10 PCS (772 g/10 PCS)
GPPC4IG7Y	7 FT. (2134mm)	2.17 LB/10 PCS (984 g/10 PCS)
GPPC4IG9Y	9 FT. (2743mm)	2.70 LB/10 PCS (1226 g/10 PCS)
GPPC4IG14Y	14 FT. (4267mm)	4.03 LB/10 PCS (1827 g/10 PCS)
GPPC4IG20Y	20 FT. (6096mm)	5.62 LB/10 PCS (2550 g/10 PCS)
GPPC4IG1MY	1 METER	.97 LB/10 PCS (439 g/10 PCS)
GPPC4IG2MY	2 METERS	1.71 LB/10 PCS (775 g/10 PCS)
GPPC4IG3MY	3 METERS	2.45 LB/10 PCS (1111 g/10 PCS)
GPPC4IG5MY	5 METERS	3.93 LB/10 PCS (1783 g/10 PCS)

PART NUMBER		GPPC4IGXXY, GPPC4IGXMY	
TITLE			
GP6 PLUS PATCH CORDS			
CUSTOMER DRAWING			
ITEM REVISION NAME		M02479NT/00	
DATASET FILE NAME		m02479NT_DC358/00B	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		MATERIAL:	
.x ±		.xxx ± .010 (.3)	
.xx ± .03 (.8)		ANGLES ±	
THIRD ANGLE PROJECTION		DRAWING NUMBER:	
02479-358		02479-358	
DRAWN BY	DATE	CHK	SCALE
NER	3-21-06	WJC	NONE
SHT 1 OF 1			SIZE
			A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
1	5/30/14	JSP	REFR	MMR	A. REVISED DRAWING TITLE BLOCK.	02479-358
R	3-21-06	NER	WJC	RMD	RELEASED TO PRODUCTION	02479-358

D10100DA/14