THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP. LABEL NOTES: **CASSETTE** ROLL MP CASSETTE "A" 1. THESE CASSETTES CONTAIN INK RIBBON AND COMPATIBLE WIDTH "B" COLOR MATERIAL LENGTH PRINTABLE MEDIA. +/-.030 **PRINTERS** PART NO. REF +10% / -0% 2) THE PRODUCTS CAN BE PRINTED WITH [0.76]PANDUIT PRINTERS (SOLD SEPARATELY), AS LISTED IN THE TABLE. 0.465 0.87 **BLACK ON** MP75, MP100, T050X000C1M-BK 3) WHEN PRINTING WITH THE MP100, [11.82] [22.1] WHITE MP200, MP300 SCISSORS SHOULD BE USED, TO CUT THE 19 ft PRINTED TAPE. 0.702 0.99 **BLACK ON** MP75, MP100, GMC6 T075X000C1M-BK 4) SEE Panduit.com FOR MORE INFORMATION. [6 m] [17.82][25.1] WHITE MP200, MP300 0.938 1.10 **BLACK ON** MP100, T100X000C1M-BK В В [23.82] [27.9] WHITE MP200, MP300 - "∧" → — 2.53 [64] — **>** 2.95 [75.00] LABEL SIDE **BACKSLIT** LINER-SIDE VIEW TITLE MP NYLON CLOTH TAPE CASSETTE T**X000C1M-BKCUSTOMER DRAWING ITEM REVISION NAME 100743XX/00 DATASET FILE NAME 100743XX_DC/00A MATERIALS UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: IN [mm] SEE TABLE .x ± .1 [2.54] .xxx ± .025 [.635] .xx ± .05 [1.27] ANGLES ± THIRD ANGLE 00A 11/03/21 |ARHA| KJM | MSAD | DRAWING RELEASE. **GAECN06410** I00743XX_DC **PROJECTION** DRAWN BY DATE SCALE DATE CHK APR DESCRIPTION ECN BY ARHA 11/03/21 **MSAD** NTS SHT 1 0F 1 2