

THIS COPY IS PROVIDED ON A	RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTEREST:	S OF PANDUIT CORP.

Material	High Conductivity Seamless Copper Tube				
Plating	Electro-Tin				
Wire Size	3/0 AWG				
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric				
Wire Strip Length	1-9/16 in.				
Stud Size	3/8 in.				
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.				
UL Temperature Rating	90° C				
C.S.A Certified Wire Connector	Yes				
Panduit Color Code on Barrel	ORANGE				
Panduit Die Index No. on Barrel	P50				
Alternate Industry Die Index No. () on Barrel	(14)				









								CORP. TINLEY PARK, ILLINOIS
								LCC3/0-38DW-X
01	8/12	JHNU	JHNU	REMOVED NAVY NUMBER	N10883US-LCC3/0-38DW-CUST	RGB	RGB	LCC3/0-38DW-X Copper Lug - Two-Hole, Long Barrel with Window
REV	DATE	BY	СНК	DESCRIPTION	ECN	-R	SUP	SCALE N/A DRAWING NO / CAD FILE LCC3_0-38DW-CUST