




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



- NOTES:
- SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
  - VISIT OUR ON-LINE CATALOG AT [WWW.PANDUIT.COM](http://WWW.PANDUIT.COM) FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
  - MATERIALS:
    - A. MODULE MATERIAL: PLASTIC
    - B. ADAPTER: COMPOSITE PLASTIC
  - FIBER ROUTING: SEE SHEET 2.
  - PART NUMBERS: SEE SHEET 2.
  - CASSETTE MODULE WEIGHT: 2.4oz [69.0g]
  - DIMENSIONS IN BRACKETS ARE METRIC.
  - PINNED FOR METHOD B MPO ASSEMBLIES.


FIBER COLOR KEY	
FIBER 1 - BLUE	FIBER 7 - RED
FIBER 2 - ORANGE	FIBER 8 - BLACK
FIBER 3 - GREEN	FIBER 9 - YELLOW
FIBER 4 - BROWN	FIBER 10 - VIOLET
FIBER 5 - SLATE	FIBER 11 - ROSE
FIBER 6 - WHITE	FIBER 12 - AQUA

FIBER TYPE	ADAPTER COLOR (SPLIT SLEEVE)
OM4	AQUA (ZIRCONIA)
OS2	BLUE (ZIRCONIA)

PART NUMBER		SEE PAGE 2	
TITLE			
QUICKNET SFQ SERIES FRONT ACCESS CASSETTE, 8 FIBER DUPLEX LC TO MPO			
CUSTOMER DRAWING			
ITEM REVISION NAME		MO2947Z1/00	
DATASET FILE NAME		MO2947Z1_DC/00C	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.X ±		.XXX ±	
.XX ±		ANGLES ±	
		THIRD ANGLE PROJECTION	
DRAWN BY		SCALE	
JSP		NONE	
DATE		SHT 1 OF 2	
5/24/23		A	
CHK		DRAWING NUMBER:	
WJM		MO2947Z1-DC	
APR		SIZE	
DESCRIPTION		A	
ECN			

D10100DA/14

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



QUICKNET SFQ FRONT ACCESS 8 FIBER LC CONVERSION CASSETTE - METHOD B	
FQF3ZO-08-10B	8 FIBER / OM4 OPTIMIZED LOSS
FQF39N-08-10B	8 FIBER / OS2 STANDARD LOSS

QUICKNET SFQ FRONT ACCESS 8 FIBER LC CONVERSION CASSETTE - METHOD U	
FQF3ZO-08-10U	8 FIBER / OM4 OPTIMIZED LOSS
FQF39N-08-10U	8 FIBER / OS2 STANDARD LOSS

QUICKNET SFQ FRONT ACCESS 8 FIBER LC CONVERSION CASSETTE - METHOD U2	
FQF3ZO-08-10U2	8 FIBER / OM4 OPTIMIZED LOSS
FQF39N-08-10U2	8 FIBER / OS2 STANDARD LOSS

FIBER POSITION FROM LC END TO MPO END								
MM METHOD B 8 FIBER CASSETTE								
LC PORT NUMBER	1		2		3		4	
	A	B	A	B	A	B	A	B
MPO** FIBER POSITION	1	12	2	11	3	10	4	9
SM METHOD B 8 FIBER CASSETTE								
LC PORT NUMBER	1		2		3		4	
	A	B	A	B	A	B	A	B
MPO* FIBER POSITION	12	1	11	2	10	3	9	4
METHOD U 8 FIBER CASSETTE (MM & SM)								
LC PORT NUMBER	1		2		3		4	
	A	B	A	B	A	B	A	B
MPO* FIBER POSITION	12	1	11	2	10	3	9	4
METHOD U2 8 FIBER CASSETTE (MM & SM)								
LC PORT NUMBER	1		2		3		4	
	A	B	A	B	A	B	A	B
MPO* FIBER POSITION	1	12	2	11	3	10	4	9

(\*) KEY UP/ KEY DOWN ADAPTER (BLACK COLOR).  
 (\*\*\*) KEY UP/ KEY UP ADAPTER (GRAY COLOR).

PART NUMBER		SEE PAGE 2	
TITLE			
QUICKNET SFQ SERIES FRONT ACCESS CASSETTE, 8 FIBER DUPLEX LC TO MPO			
CUSTOMER DRAWING			
ITEM REVISION NAME		M02947Z1/00	
DATASET FILE NAME		M02947Z1_DC/00C	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		MATERIAL:	
.X ± .XX ±		.XXX ± ANGLES ±	
		DRAWING NUMBER: M02947Z1-DC	
DRAWN BY	DATE	CHK	SCALE
JSP	5/24/23	WJM	NONE
SHT 2 OF 2			SIZE A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
					SEE PAGE 1 FOR REVISION HISTORY	

D10100DA/14