| THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP. |  |                                  |
|--|--|----------------------------------|
| Material   | High Conductivity<br>Seamless Copper Tube  |                                  |
| Plating  | Electro-Tin  |                                  |
| Wire Size  | 750 STR/FLEX   | 56 F                             |
| Wire Type  | Stranded Copper:<br>Locomotive   |                                  |
| Wire Strip Length  | 1-3/4 in.  |                                  |
| Stud Size  | 3/8 in.  |                                  |
| UL Listed Wire<br>Connector  | Yes, for applications up to 35kv.<br>Consult cable manufacturer for<br>voltage stress relief instructions<br>with applications greater than<br>2000 volts. | .50±.07 1.00±.0241±.0<br>(2) PLS |
| UL Temperature<br>Rating   | 90°C   |                                  |
| C.S.A Certified<br>Wire Connector  | Yes  |                                  |
| Panduit Color Code<br>on Barrel  | YELLOW   | Wire inspection window 1.        |
| Panduit Die Index No.<br>on Barrel   | P115   |                                  |
| Alternate Industry<br>Die Index No. ( )<br>on Barrel   | (L115)   |                                  |
|  |  | .38±.01 —                        |
| CERTIFIED  | D LISTED<br>Wire Connector   |                                  |

JHNU JHNU REVISED OVERALL LENGTH: WAS 3.74 REVISED TONGUE THICKNESS: WAS .22

05

REV

1/11

DATE

ΒY

CHK

