2			1				
THIS COPY IS PROVIDE	D ON A RESTRICTED BASIS AND IS NOT TO BE US	ed in any w	AY DETRIMEN	ITAL TO THE INTEREST	S OF PANDUIT CORP.	_	
				PANDUIT P/N	WEIGHT		
			NOTES:	UICFP2S	1.47 LB/10 PCS (668.3g/10 PCS)		
B 4.51 [114.5]	2.76 [70.0] [8.3] [8.3] [3.28 [83.3] [83.3]		1. SEE PART COLC 2. SEE PART 3. DIME METF 4. PART 1- C 1- C 1- C	NUMBER SUFFIXE Or and or packag catalog for com s applicable fo	GE QUANTITY. Aplete list of or use with this otheses are in er ed screw cover	В	
						4	
	_19.1		PART NUMBER				
				UICFP2S			
A			MINI-COM ULTIMATE ID 2 POSITION STAINLESS STEEL FACEPLATE CUSTOMER DRAWING				
			ITEM REVISION NAME				
			DATASET FILE NAME	M02237AA_DC/01B	PANDUN		
			DIMENSIONAL	OTHERWISE SPECIFIED, TOLERANCES ARE: IN [mm .xxx : .010 [.3]	304 STAINI ESS STEEL		
[★] 1 5-20-14 BJN JSP MMR	IR REVISED & REDRAWN PREVIOUS REVISIONS REMVD FOR CLARITY		3.]EO. ± ××.	THIRD ANGLE	DRAWING NUMBER:		
1 5-20-14 BJN JSP MMR 000000000000000000000000000000000000	REV DATE BY CHK APR DESCRIPTION		DRAWN BY DATE	4-07 JC0 NONE	SHT 1 0F 1	SIZE	
2					I	<u>`</u>]	