| Materi | rial | | | High Conductivity Seamless Copper Tube |] | | | | | |
|--|-------|-------|----------|--|-------------------------|--------|--|--|--|--|
| Plating | g | | | Electro-Tin | | | | | | |
| Wire Size | | | | 250 kcmil | | | | Color coded / Color markings | | |
| Wire Type | | | | Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric | | DUIT | 250 STR CU LCC250-00 | | | |
| Wire Strip Length | | | | 1-11/16 in. | - 1.17±.04 | A NI | 50 ST CC2! | | | |
| Stud Size | | | | N/A | ┨ _╉└ | ₫ | с N Ц | | | |
| UL Listed Wire Connector | | | | Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts. | - | | | 5.23±.06 | | |
| UL Temperature Rating | | | 90° C | | | | | | | |
| C.S.A Certified Wire Connector | | | | Yes | | | | | | |
| Panduit Color Code on Barrel | | ode | YELLOW | | | | - 1.60±.04 - Beveled wire entry | | | |
| Panduit Die Index No. on Barrel | | x No. | P62 | | - 3.00 | ±.04 - | .63±.01 .77±.01 | | | |
| Alternate Industry Die Index No. () on Barrel | | | У | (16) | | | | | | |
| | | CE | | RECOGNIZED Wire Connector | 14±.01 | | | | | |
| | | | | | | | | CORP. TINLEY PARK, ILLINOI | | |
| 1 5/ | /12 . | JHNU | RGB | REMOVED NAVY NUMBER FROM TONGUE | N10883DG-LCC250-00-CUST | RGB | RGB | LCC250-00-X | | |
| 0 12/02 SAB DRL | | DRL | RELEASED | 10333 | | | Copper Lug - Blank Tongue, Long Barrel | | | |
| EV DA | ATE | BY | СНК | DESCRIPTION | ECN | -R | SUD | SCALE N/A DRAWING NO / CAD FILE LCC250-00-CUST | | |