NetKey® Surface Mount Boxes



specifications

Surface mount boxes shall have a low profile design and shall be available in a variety of port densities. Boxes shall accept all NetKey Keystone Modules for fiber, copper, audio, and video applications. The boxes shall mount with screws, adhesive, or optional magnets and shall include breakouts for use with surface raceway. Cable tie slots shall be included to provide strain relief on incoming cables.



technical information

Mounting options:	Mounts easily with screws, adhesive tape, or optional magnet
Material:	Box is made of ABS

key features and benefits

Modular	Accepts all NetKey Keystone Modules which snap in and out for easy moves, adds, and changes			
Low profile design	Presents a more discreet or inconspicuous look			
Raceway breakouts	Compatible with specific surface raceway, conceals cable entering the box			
Cover screw	Select boxes provide a screw that secures the cover to the base			
Labels and label covers	Select boxes include a label pocket to meet labeling standards			
Magnet pockets	Accept magnets for mounting on metal surfaces; NK2BX*-A, NK4BX*-AY			

Part Number	Compatible Raceway	No. of Adhesive Strips	No. of Cable Ties	Label/Label Cover Included	Mounting Screws Included	Magnet Pockets
NK2BX	LD3, LD5	1	1	No	Yes	1
NK4BX	LD3, LD5	2	2	Yes	Yes	2
NK6BX	LD3, LD5	2	2	Yes	Yes	None

applications

NetKey Surface Mount Boxes offer a variety of mounting options, allowing NetKey Keystone Modules to mount on a variety of surfaces such as standard walls, metal surfaces, office furniture and more. Surface mount boxes include Surface Raceway compatible breakouts to allow cable to run discretely into the box to provide a point of connection for voice, video, and data applications.

∕ Surface	

2-port: NK2BXIW-A^
4-port: NK4BXIW-AY
6-port: NK6BXIW-AY

Accessories


Blank Module: NKBMIW-X-L Magnet: CBM-X


^{*}For standard colors other than IW (Off White), replace suffix with EI (Electric Ivory), WH (White), IG (International Gray), or BL (Black).

[^]Suitable for air handling spaces.


NetKey® Surface Mount Boxes

2-Port Surface Mount Box NK2BXIW-A







Drawing shown with blank module breakout. Remove breakout for two positions.




4-Port Surface Mount Box NK4BXIW-AY







(3 Places)



6-Port Surface Mount Box NK6BXIW-AY





Dimensions are in inches. [Dimensions in brackets are metric].

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575

PANDUIT JAPAN Tokyo, Japan Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

