




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT P/N	WEIGHT
JFPAOSPTP**	.23 LB/10 PCS (106.2 g/10 PCS)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. PARTS INCLUDED IN KIT:
(1) - ADAPTER
(1) - MINI-COM TX6 PLUS JACK MODULE



VIEW SHOWN WITH A MINI-COM TX6 PLUS JACK MODULE INSTALLED



PART NUMBER		JFPAOSPTP**	
TITLE			
MINI-COM 1 POSITION JIS ADAPTER KIT			
CUSTOMER DRAWING			
ITEM REVISION NAME		M00741SZ/00	
DATASET FILE NAME		M00741SZ_DC17/00A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		MATERIAL:	
.x ± .xx ± .03 (.8)		ADAPTER - ABS DOOR - PC	
.xxx ± .010 (.3)		DRAWING NUMBER:	
ANGLES ±		00741-17	
THIRD ANGLE PROJECTION		SHT 1 OF 1	
DRAWN BY	DATE	CHK	SCALE
JSP	2-6-03	PBD	NONE
REV	DATE	BY	CHK
3	6-25-14	MDJR	REFR
APR	DESCRIPTION		ECN
MMR	A. UPDATED TITLE BLOCK. REMOVED ALL PREVIOUS REVISIONS FOR CLARITY.		00741-17

D10100DA/14

2

1

2

1