




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
JAOSSP6TG**	.28 LB/10 PCS (127 g/10 PCS)




NOTES:

- SEE PANDUIT WEBSITE FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
- SEE PANDUIT WEBSITE FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.
- PART INCLUDES:
 - 1- ADAPTER WITH OPAQUE DOOR AND LAN/CAT6 PRINT
 - 1- MINI-COM CAT6 JACK MODULE



VIEW SHOWN WITH A STANDARD TERMINATION CAP.



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
02B	8-7-23	BJN	MDJR	MMR	REMOVED NOTE & IMAGE OF RIGHT ANGLED WIRE CAP	02079CB-01
2	5-24-18	TWV	MDJR	MMR	ADDED NOTE & IMAGE OF RIGHT ANGLED CAP	02079CB-01
1	6-28-17	BJN	MDJR	MMR	REMOVED NOTE & IMAGE OF RIGHT ANGLED CAP	02079CB-01
R	9/06/16	MDJR	NAGL	MMR	RELEASED TO PRODUCTION	02079CB-01

TITLE MINI-COM 1 POSITION JIS SPRING SHUTTERED ADAPTER KIT					
CUSTOMER DRAWING					
ITEM REVISION NAME M02079CB/02				PANDUIT	
DATASET FILE NAME M02079CB_DC/02B					
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)					
.x ± .1 [2.54]		.xxx ± .005 [.127]		MATERIAL: ADAPTER- ABS DOOR- ABS SPRING- SPRING STEEL	
.xx ± .01 [.25]		ANGLES ± 5 °		DRAWING NUMBER: 02079CB-01	
DRAWN BY MDJR			DATE 6/29/16		CHK MMR
SCALE NONE			THIRD ANGLE PROJECTION		SIZE A
SHT 1 OF 1					

D101000DA/14