						2				1			
		THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE US						ED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.					
										PANDUIT RT NUMBER	WEIGHT		
							NOTES:			R12TB2412 12TB2412M	4.49 LB/EACH (2037 ₉ /EACH)		
в					2)	[55.7]	TO INE 24" WI FIBERF TWO (2 THAT A 3. THE FI 24" WI INCLUE ONE (1 TWO (2 FOUR (FOUR (FOUR (ONE (1 ONE (1 ONE (1 4. FINISH	DICATE [BERRL [DE CA RUNNEF 2) SEC ARE 24 [BERRL [DE CA DES: [] BRA 2) 1/2 [4] 1/2 [4] 1/4 [] 1/4-] 1/4-] COLC	E PACKAGI JNNER 12: ABLE PATI 12×4 C CTIONS OI WICKET AS ABLE PATI ACKET AS CLAMP P CLAMP P C CLAMP P C CLAMP P C CLAMP P C C C C C C C C C C C C C C C C C C	E QUANTITY ×4 QUIKLOCH HWAYS IS US ABLE ROUTIN T NEW 1/2" 6) - 31.5" ×4 QUIKLOCH HWAYS - 1/2 SEMBLY, LATES, L SPRING LO VY HEX NUTS HEX NUTS (F LT, KEPS NUT. < (EXCEPT F	K TRAPEZE BRACKET FOR SED TO SUPPORT THE NG SYSTEM BETWEEN (M12) THREADED ROD (800.1) APART. K TRAPEZE BRACKET FOR	в	
$\langle -$		•				2.00							
	[12.8] 	ר יי ון		AMPING · PTIONAL				
								FIBERR	UNNER 12×	4 QUIKLOCK TR	APEZE BRACKET FOR 24" WIL)E	
Α								-		THWAYS - 1/3	2" (M12) THREADED ROD	A	
								ITEM REVIS	D3970	CUSTOMER			
								DATASET FI	LE NAME	S_DC/00B	— Panduit		
			MEX-										
S	00B	9/9/19 10/21/08	JAGC MS0	FWI SL	FWI	A. "STAMPING OPTIONAL" LABEL ADDED SEE PREVIOUS REVISION FOR HISTORY RELEASED TO PRODUCTION	V09002CN/07 39701-48		-				
2/V000	R Rev									THIRD ANGLE PROJECTION	SI	IZE	
D101	REV	DATE	BY	СНК	APR		ECN	MS0	10/21/08	SL NONE	SHT 1 OF 1 /	4	
						2				1			