

specifications

There are two different Ingress/Egress Kits that are used with the 150mm Vertical Cable Managers: Slack Spool Manager kit (FDFSPLKITBL) and Cable Breakout Box Kit (FDFMX5KITBL). The Slack Spool Manager provides slack management for both factory terminated trunks and field spliced cabling. The Cable Breakout Box Kit allows higher fiber count trunk cables to be broken down into smaller fiber counts to easily feed the 24 fiber cassettes. It provides an anchor for the outer jacket and central strength member(s) of the cabling. The Cable Breakout Box Kit comes with twelve 2 foot protective flexible tubes but additional protective flexible tubing can be ordered.



Slack Spool Manager Kit



Cable Breakout Box Kit with Protective Flex Tubing

FDFSPLKITBL slack spool manager kit

Feature	Benefit
Slack management	Ensures proper slack management for factory terminated breakout lengths on trunk cables to enable easier installation
Mounting flexibility	Can be mounted anywhere on TIA/EIA mounting holes located on the rack

FDFMX5KITBL cable breakout box kit

Feature	Benefit
Holder	Holds up to 36 Flex Tubes
Pre-packaging	Includes (12) 5.0mm diameter Flex Tubes precut in length to 2'
Breakout of full cable range	Breaks out cable diameter up to 1.3" (33mm)
Flexibility of fiber type which can be used	<ul style="list-style-type: none"> • 2 flat ribbons/Flex Tube • 48 loose 250 micron fibers/Flex Tube • 4 rollable ribbons/Flex Tube • (6) 900µm fibers/tube
Breakout to multiple enclosures	Additional lengths of Protective Flexible Tubing are available to allow breakout to multiple enclosures in system
Off-the-frame splicing	Ability to completely strip, breakout and splice cables to cassettes off the frame
Mounting to vertical cable managers (VCM)	Mounts onto 150mm VCM ingress/egress plates sold separately
Lock down robustness	Secures high count and bulk cable outer jacket and central strength members
Breakout cable count flexibility	Can break out multiple cable counts, from 24 – 864 fibers

*Reference FS206 for latest ingress/egress installation instructions

Additional Protective Flexible Tubing	Length of Tubes	Quantity of Tubes
FM5PPBLF2.0-12	2'	12
FM5PPBLF4.0-12	4'	12
FM5PPBLF8.0-12	8'	12

Type of Fiber	Maximum Quantity of Fibers per Tube
Rollable/Spiderweb Ribbon	48
250µm Loose Tube	36
Flat Ribbon	24
900µm Tight Buffer	6

FlexCore™ Ingress Egress Kit

general specifications

Access	Front
Application	Cable breakout and slack management
Color	Black
Units	1

environmental specifications

Environment	Indoor
Standards	RoHS

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com
Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

PANDUIT®

© 2022 Panduit Corp.
ALL RIGHTS RESERVED.
FBSP216--WW-ENG
1/2022