

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	DESCRIPTION	SINGLE HINGE FRONT DOOR	SPLIT REAR DOOR	SPLIT SIDE PANEL	FRONT CAGE NUT E-RAIL	REAR CAGE NUT FINGER MGMT E-RAIL	REAR CAGE NUT VERTICAL PATCH E-RAIL	STANDARD PDU BRACKETS	CASTERS	CABLE MGMT FINGERS	VERTICAL PATCHING	CABINET WEIGHT FULLY UNPACKAGED	CABINET WEIGHT SHIPPING WEIGHT
S7222*	NET-ACCESS S-TYPE CABINET 700mm X 42RU X 1200mm DEEP	01	01	02	02	02	00	02	04	00	00	139 Kg/EACH 307 LBS/EACH	160 Kg/EACH 352 LBS/EACH
S7522*	NET-ACCESS S-TYPE CABINET 700mm X 45RU X 1200mm DEEP	01	01	02	02	02	00	02	04	00	00	146 Kg/EACH 322 LBS/EACH	166 Kg/EACH 367 LBS/EACH
S7822*	NET-ACCESS S-TYPE CABINET 700mm X 48RU X 1200mm DEEP	01	01	02	02	02	00	02	04	00	00	153 Kg/EACH 337 LBS/EACH	173 Kg/EACH 382 LBS/EACH
S7229*	NET-ACCESS S-TYPE CABINET 700mm X 42RU X 1200mm DEEP	01	01	00	02	02	00	02	04	00	00	99 Kg/EACH 219 LBS/EACH	120 Kg/EACH 264 LBS/EACH
S7529*	NET-ACCESS S-TYPE CABINET 700mm X 45RU X 1200mm DEEP	01	01	00	02	02	00	02	04	00	00	106 Kg/EACH 235 LBS/EACH	127 Kg/EACH 280 LBS/EACH
57829*	NET-ACCESS S-TYPE CABINET 700mm X 48RU X 1200mm DEEP	01	01	00	02	02	00	02	04	00	00	113 Kg/EACH 250 LBS/EACH	134 Kg/EACH 295 LBS/EACH
S7222*F	NET-ACCESS S-TYPE CABINET 700mm X 42RU X 1200mm DEEP	01	01	02	02	02	00	02	04	01	00	140 Kg/EACH 309 LBS/EACH	160 Kg/EACH 354 LBS/EACH
S7522*F	NET-ACCESS S-TYPE CABINET 700mm X 45RU X 1200mm DEEP	01	01	02	02	02	00	02	04	01	00	147 Kg/EACH 324 LBS/EACH	167 Kg/EACH 369 LBS/EACH
S7822*F	NET-ACCESS S-TYPE CABINET 700mm X 48RU X 1200mm DEEP	01	01	02	02	02	00	02	04	01	00	154 Kg/EACH 339 LBS/EACH	174 Kg/EACH 384 LBS/EACH
S7229*F	NET-ACCESS S-TYPE CABINET 700mm X 42RU X 1200mm DEEP	01	01	00	02	02	00	02	04	01	00	100 Kg/EACH 221 LBS/EACH	121 Kg/EACH 266 LBS/EACH
S7529*F	NET-ACCESS S-TYPE CABINET 700mm X 45RU X 1200mm DEEP	01	01	00	02	02	00	02	04	01	00	107 Kg/EACH 237 LBS/EACH	128 Kg/EACH 282 LBS/EACH
S7829*F	NET-ACCESS S-TYPE CABINET 700mm X 48RU X 1200mm DEEP	01	01	00	02	02	00	02	04	01	00	114 Kg/EACH 252 LBS/EACH	135 Kg/EACH 297 LBS/EACH

\* DENOTES COLOR "B" = BLACK "W" = WHITE

A								NET-ACCESS S TYP 700mm WIDE X 1200mm		
								CUSTOMER DRAWING		
								12V305TK/03.PRT  DATASET FILE NAME 12V305TK_DC/03A.PRT	PANDUIT	
-								MATE	ERIAL:	
	OBA	8/20/2020	RAMA	ELE	ELE	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX		N1. 6A	
	00B	5-14-13	MDCA	JDW	JDWE	SEE SHEET 1 OF 5 FOR REVISIONS	12V305TK-DC	DDA	N/A	
	00A	8-29-12	TWV	JDW	PBD	SEE SHEET I OF 5 FOR REVISIONS	12V305TK-DC	THIRD ANGLE PROJECTION	12V305TK-DC	
	REV	DATE	BY	СНК	APR	DESCRIPTION	ECN	DRAWN BY DATE CHK SCALE TWV 8-29-12 JDW NONE	SHT 2 OF 5	





