



Part Number: P12PF

Product Description: STUD WALL CLIP WITH 3/4" PUSH FIT CONDUIT CLIP

**Material Specifications**

Type: Assembly

Finish: Assembly

Color: Various

**Function Specifications****Compatible Wires and Cables**

AC/MC CABLE (OD):

Drop Wire:

Plain Rod (in):

**Threaded Rods and Bolts**

Tapped Holes:

Clearance Holes (in): 1/4

Threaded Rod Size (in):

**Compatible Conduit**

EMT Size (in): 3/4

Rigid/IMC (in): 1/2

**Compatible Flanges and Studs**

Flange Size (in):

Metal Stud Size (ins): Most standard 1-3/8" width

**Static Load Rating**

Vertical (lbs):

Horizontal (lbs):

**Other****Codes and Regulatory**Regulatory  
Certifications:

Country of Origin: US

**Packaging**

General Packaging: Cardboard Box

Box Size: 15 X 8.25 X 7.25

Pieces per Package: 100

Other Box Features:

**Document Information**

Created By: DBLA

Checked By: DJW

Approved By: KLN

Customer Specification #: C11318

Revision Level: 01

ECN #: GAECN01482

Date: 12/10/2013