
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	24 × 44	** T **	**R**	44 L 44	** G **	WE I GHT
SD2H6	1.785 ±.030	.065 ±.012	.235 ±.027	1.180 ±.030	.80 ±.04	.077 LB/FT
	(45.34 ±.8)	(1.7 ±.3)	(6.0 ±.7)	(29.9 ±.8)	(2.0 ±1.0)	(.115 Kg/M)
SD3H6	2.743 ±.050	.085 ±.016	.255 ±.027	2.108 ±.030	1.00 ±.04	.132 LB/FT
	(69.67 ±.1.3)	(2.1 ±.4)	(6.48 ±.7)	(55.4 ±.8)	(25.4 ±1.0)	(.197 Kg/M)
SD4H6	3.533 ±.0.06	.110 ±.020	.255 ±.027	2.903 ±.030	1.00 ±.04	.288 LB/FT
	(89.75 ±1.52)	(2.8 ±.5)	(6.48 ±.7)	(73.7 ±.8)	(25.4 ±1.0)	(.429 Kg/M)



NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.

B

- 2. THIS PART IS INTENDED TO BE USED WITH MOUNTING BASE DB-C OR DBM-C IN ORDER TO SUCCEED AS A DIVIDER WALL APPLICATION.
- 3. DIMENSIONS IN PARENTHESES ARE METRIC.

