

# Bulk Packed Jacks



## Our Commitment to the Environment

Some of the most common products manufactured for networking projects are connectors – mainly jacks and patch cords. Bulk packed jacks are faster and easier to install, and drastically reduce single-use plastic.

### APPLICATION BENEFITS

Bulk jacks are offered in 24 and 100 unit packs.

Each module is 100% factory tested for continuity. TG style termination eliminates the need for a punchdown termination tool. Each jack is individually serialized for traceability and is compatible with Mini-Com Modular Patch Panels and Faceplates.

## Reduce Waste

- 99% reduction in single-use plastic
- 74% reduction in total waste by weight

## Reduce Time & Labor

- 98% reduction in time required to open packaging

## Reduce Freight Costs

- 50% reduction in freight volume

#### Carbon Footprint Reduction

Move to renewable energy sources and carbon neutrality

#### Drive Sustainable Product Innovation

Increase offering of products designed and developed with sustainability in mind



#### Support the Circular Economy

Convert to post-consumer materials for products and packaging

#### Eliminate Waste

Attain zero waste to landfill



DOWNLOAD

Sustainability Brochure

Panduit Environmental, Social, and Governance Report

# Ordering Guide

## Jacks – 24 Packs

Category 6A	Category 6	Category 5e
CJ6X88TGBL-24 ★	CJ688TGBL-24 ★	CJ5E88TGBL-24
CJ6X88TGBU-24 ★	CJ688TGBU-24 ★	CJ5E88TGBU-24
CJ6X88TGWH-24 ★	CJ688TGWH-24 ★	CJ5E88TGWH-24
CJ6X88TGEI-24	CJ688TGEI-24	CJ5E88TGEI-24
CJ6X88TGIG-24	CJ688TGIG-24	CJ5E88TGIG-24
CJ6X88TGIW-24	CJ688TGIW-24	CJ5E88TGIW-24
CJ6X88TGAW-24	CJ688TGAW-24	CJ5E88TGAW-24
CJ6X88TGRD-24	CJ688TGRD-24	CJ5E88TGRD-24
CJ6X88TGOR-24	CJ688TGOR-24	CJ5E88TGOR-24
CJ6X88TGYL-24	CJ688TGYL-24	CJ5E88TGYL-24
CJ6X88TGGR-24	CJ688TGGR-24	CJ5E88TGGR-24
CJ6X88TGVL-24	CJ688TGVL-24	CJ5E88TGVL-24

### Shielded

CJS6X88TGY-24	CJS688TGY-24
---------------	--------------

## Jacks – 100 Packs

Category 6A	Category 6
CJ6X88TGBL-C ★	CJ688TGBL-C ★
CJ6X88TGBU-C ★	CJ688TGBU-C ★
CJ6X88TGWH-C ★	CJ688TGWH-C ★
CJ6X88TGEI-C	CJ688TGEI-C
CJ6X88TGIG-C	CJ688TGIG-C
CJ6X88TGIW-C	CJ688TGIW-C
CJ6X88TGAW-C	CJ688TGAW-C
CJ6X88TGRD-C	CJ688TGRD-C
CJ6X88TGOR-C	CJ688TGOR-C
CJ6X88TGYL-C	CJ688TGYL-C
CJ6X88TGGR-C	CJ688TGGR-C
CJ6X88TGVL-C	CJ688TGVL-C

★ = Best Seller and Featured Products

AW = Arctic White  
 BL = Black  
 BU = Blue  
 EI = Electric Ivory

GR = Green  
 IG = International Gray  
 IW = Off White  
 OR = Orange

RD = Red  
 VL = Violet  
 WH = White  
 YL = Yellow

