




PANDUIT P/N	WEIGHT
P22B39M	2.0kg




REAR VIEW



TOP VIEW



FRONT VIEW



SIDE VIEW

- NOTES:
- IDENTIFICATION:

UNIT TYPE:	BASIC
ORIENTATION:	VERTICAL, HALF
OUTLET QTY&TYPE:	(20) C13, (2) C19
BREAKER QTY&TYPE:	N/A
INPUT VOLTAGE:	100-240VAC
INPUT CURRENT:	16A
INPUT PHASE:	SINGLE-PHASE
RATED POWER:	3.7kVA
INPUT PLUG:	IEC 60309 2P+E 6H 16A
INPUT CORD LENGTH:	3m [10']
 - ACCESSORIES:
 - POCKET GUIDE
 - RoHS COMPLIANT
 - VISIT PANDUIT'S ON-LINE CATALOG AT WWW.PANDUIT.COM FOR ADDITIONAL PRODUCT INFORMATION CONTAINED IN THE SPECIFICATION SHEET AS WELL AS A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
 - MAXIMUM ALLOWABLE INPUT POWER = 3.7kW
 - INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES

PLUG
16 AMP, 250V
2P/3W
IEC 60309, SPLASHPROOF, IP44
3H (S); 3R (W), 6H

TWO (2) RECEPTACLES
16 AMP, 250V
STRAIGHT BLADE
IEC 60320 / C19

TWENTY (20) RECEPTACLES
10 AMP, 250V
STRAIGHT BLADE
IEC 60320 / C13

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
01B	08/21/2017	ZHAI	MIM	EDM	REVISED TOLERANCES	P22B39M
01A	06/28/2017	ZHAI	MIM	EDM	INITIAL RELEASE	P22B39M

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY

SIGN	DATE	PRINT
TITLE: BASIC SERIES PDU P22B39M CUSTOMER DRAWING		
ITEM REVISION NAME:		
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		
Tolerance(mm)		
04<L<50	±0.5	
50<L<250	±1.0	
250<L<500	±1.5	
500<L<1000	±2.5	
1000<L<2000	±4.0	
THIRD ANGLE PROJECTION		
DRAWN BY: DI.ZHAI	DATE: 05/24/2017	SCALE: NONE
CHK: SEAN		
MATERIAL/COLOR: N/A		
DRAWING NUMBER: P22B39M_DC		
SHT 1 OF 1		SCALE: B