


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	MATERIAL	COLOR	MARKER SIZE inches [ mm ]	LABEL PER SHEET	SHEETS PER PKG.	STANDARD PKG. QTY.
C100X050AAL	GMY2-STE	SILVER	0.75 [ 19.05 ]	119	85	10000
C100X050YML	GMY2		X X 0.25 [ 6.35 ]			

NOTES:  
1. MILLIMETERS ARE IN [     ].



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
4	7/16/19	RVU	JW	JHAC	REPLACED "INKJET" TO "LASER" FROM THE HEADER DESCRIPTION.	GAECN04936
3	1/18/16	RVU	SEWH	JHAC	GMY2-STE WAS GMY4-STE.	GAECN03331
2	9/21/15	RVU	SEWH	JHAC	GMY4-STE WAS GMY2STE. GMY2 WAS GMY5. UPDATE TABLE. CHG. FORMAT B TO A. UPDATE TOL., NOTES AND TITLE. UPDATE LOGO.	GAECN03033
1	8/13/07	RVU			ADDED NEW PN, C100X050YML.	5070
0	10/27/06	RVU			DRAWING RELEASE.	4752

TITLE						
C100X050AAL AND C100X050YML LASER LABELS CUSTOMER DRAWING						
ITEM REVISION NAME					100472LT/04	
DATASET FILE NAME					100472LT_DC_C10533/04F	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]					<b>PANDUIT</b>  MATERIAL:  <b>SEE TABLE</b>	
.x ± .12 [ 3.05 ]     .xxx ± .025 [ .635 ] .xx ± .062 [ 1.57 ]     ANGLES ±						
DRAWN BY					DRAWING NUMBER:	
RVU					C10533	
DATE					SCALE	
10/27/06					NTS	
CHK					SHT 1 OF 1	
JHAC					A	
THIRD ANGLE PROJECTION						