



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. DIMENSIONS IN PARENTHESIS ARE METRIC.
3. INDEPENDENT ADJUSTABLE FRONT & REAR MOUNTING RAILS (EIA) ADJUST FROM 3.25" TO 36" DEPTH.
4. CAN BE USED WITH ANY EIA STANDARD COMPONENT IN ADDITION TO ALL PANDUIT HORIZONTAL CABLE MANAGEMENT AND PATCH PANEL PRODUCTS.
5. 52 AVAILABLE RACK SPACES.
6. EIA UNIVERSAL STANDARD HOLE PROGRESSION ON FRONT CHANNELS AND REAR MOUNT RAILS
.625", .625", .500", .625", .625", .500"...ETC.
7. ALL RACKS WILL HAVE NUMBERS UP ORIENTATION (RU "01" ON BOTTOM, RU "52" ON TOP). INSTRUCTIONS WILL BE PROVIDED ON HOW TO GET NUMBERS DOWN ORIENTATION.
8. RU SPACING NUMBERS ARE CLEARLY PRINTED ON MOUNTING RAILS.
9. ALL ASSEMBLY HARDWARE INCLUDED:
(12) 3/8-16 X 1" HEX CAP SCREW
(24) 3/8" PAINT PIERCING GROUNDING WASHER
(1) TUBE OF ANTI-OXIDIZING PASTE
(12) 3/8-16 HEX NUT
(25) 12-24 X .5" SLOTTED PAN HEAD STEEL SCREW
(25) #12-24 CAGE NUTS (ONLY PROVIDED FOR R4P36CN96(WH))
10. EASY ASSEMBLY, ONE WRENCH NEEDED TO INSTALL BOLTS INTO WELDNUTS IN ALL 8 CORNERS.
11. FULLY BONDED STRUCTURE WHEN ASSEMBLED PER INSTRUCTIONS.
12. LOAD RATING - 2500 LBS.
13. WEIGHT:
R4P3696(WH) - 120 lbs [54.5 kgs]
R4P36CN96(WH) - 110 lbs [50.0 kgs]




PART NUMBER		R4P3696, R4P3696WH, R4P36CN96, R4P36CN96WH	
TITLE		8 FOOT TALL 36" DEEP 4 POST RACK	
ITEM REVISION NAME		CUSTOMER DRAWING	
DATASET FILE NAME		V10679ZD/04	
MATERIAL		STEEL	
DRAWN BY		BAME	
DATE		7-2-09	
CHK		DSI	
SCALE		NONE	
DRAWING NUMBER		V10679ZD-DC	
SHEET 1 OF 3		A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
04A	3-23-23	TWV	MPOL	KCOR	UPDATED DRAWING	V10679ZD


2

1


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



FLOOR FOOTPRINT WITH
BASE ANGLES TURNED
OUTWARD FOR EXTENDED
FOOTPRINT



FLOOR FOOTPRINT WITH
BASE ANGLES TURNED INWARD

PART NUMBER		R4P3696, R4P3696WH, R4P36CN96, R4P36CN96WH	
TITLE		8 FOOT TALL 36" DEEP 4 POST RACK	
CUSTOMER DRAWING			
ITEM REVISION NAME		V10679ZD/04	
DATASET FILE NAME		V10679ZD_DC/04A	
		THIRD ANGLE PROJECTION	
MATERIAL		STEEL	
DRAWING NUMBER		V10679ZD-DC	
DRAWN BY	DATE	CHK	SCALE
BAME	7-2-09	DSI	NONE
SHEET 2 OF 3			SIZE A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
04A	3-23-23	TWV	MPOL	KCOR	SEE SHEET ONE FOR REVISIONS	V10679ZD

2

1

A-SIZE CUSTOMER

A

2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

J-HOOKS UP TO 3/8" DIA. MAY BE MOUNTED TO THE RACK FROM THE FRONT OF THE RACK TOP ANGLES.

BONUS HOLES ARE FOR MOUNTING PANDUIT ACCESSORIES. SEE NOTE 1

MOUNTING HOLES FOR OPTIONAL POWER STRIP BRACKET. BRACKETS CAN BE MOUNTED ON ANY OF THE 4 POSTS OR ADJUSTABLE RAILS.

OPTIONAL POST HOLES FOR BRACKET MOUNTING NETRUNNER

MASKED AREA FOR GROUNDING, TOP & BOTTOM OF RACK, 4 PLACES

BASE ANGLES (SEE SHEET 2 FOR MOUNTING POSITIONS)

"J" BOLT MOUNTING HOLES FOR SECURING LADDER RACK PERPENDICULAR AND PARALLEL TO 4 POST RACK.

MOUNTING RAILS (ADJUSTABLE FROM 3.25" TO 36")

CUTOUTS FOR MOUNTING PANDUIT ACCESSORIES SEE NOTE 1.

CROSS BEAMS ARE MARKED EVERY 1/2" FOR MOUNTING RAIL ALIGNMENT

MOUNTING HOLES FOR VERTICAL MANAGERS. DOUBLE HOLES ARE FOR MOUNTING PATCHRUNNER. SINGLE HOLES ARE FOR SIDE MOUNTING NETRUNNER.

RU SPACINGS ARE PRINTED ON MOUNTING RAILS

R4P3696 (WH) RAILS HAVE TAPPED HOLES

R4P36CN96 (WH) RAILS HAVE CAGE NUT HOLES

PART NUMBER		R4P3696, R4P3696WH, R4P36CN96, R4P36CN96WH	
TITLE		8 FOOT TALL 36" DEEP 4 POST RACK	
ITEM REVISION NAME		CUSTOMER DRAWING	
DATASET FILE NAME		V10679ZD/04	
MATERIAL		STEEL	
DRAWN BY		BAME	
DATE		7-2-09	
CHK		DSI	
SCALE		NONE	
DRAWING NUMBER		V10679ZD-DC	
SHEET 3 OF 3		A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
04A	3-23-23	TWV	MPOL	KCOR	SEE SHEET ONE FOR REVISIONS	V10679ZD

2

1

B

A

A