

## GROUNDING AUXILIARY CABLE BRACKET

PART NUMBERS: GACB-2, GACB-3



© Panduit Corp. 2011 **INSTALLATION INSTRUCTIONS** T-PMPI-299-PC **GACB-3 on Wyr-Grid Pathway** GACB-2 on Wyr-Grid Pathway GACB-2 Wyr-Grid Pathway Wvr-Grid Pathway BRACKET MUST REST AGAINST WYR-GRID CROSS-WIRE BRACKET TEETH MUST MAKE GACB-3 CONTACT WITH WYR-GRID WIRE BRACKET MUST REST AGAINST (2)GACB-2 **WYR-GRID CROSS-WIRE** 24 Mounting Screw #12-24 Mounting BRACKET TEETH MUST MAKE 45 lbf-in Screw CONTACT WITH WYR-GRID WIRE 45 lbf-in [5.08 N.m] [5.08 N.m] GACB-3 #12-24 Screws (not included) **#6 AWG PRE-TERMINATED JUMPERS** GACBJ68U 8" LENGTH Paint Piercing Teeth GACBJ612U 12" LENGTH GACBJ618U 18" LENGTH ·⊕-∰- **C** 1 + + + 2 Hole, Slotted 1/4" Stud 1/2" - 5/8" Spacing Two Cable Tie **Mounting Options** (Cable Ties not included) Telecommunications Equipment Bonding Conductors (TEBC) Telecommunications Equipment Bonding Conductors (TEBC) Use GACBJ618U to bond Wyr-Grid system to ground bar Use GACBJ618U to bond

Wyr-Grid system to ground bar

## **GACB-3 on LADDER RACK GACB-2 on LADDER RACK** GACB-2 Ladder Rack Ladder Rack LADDER RACK SPECS. GACB-3 WIDTH = 3/8" HEIGHT = 1-1/2" - 2" MAX. PAINT THICKNESS = .0040" (2) SOLID OR TUBE (2)#12-24 Mounting #12-24 Mounting Screw Screw 45 lbf-in 45 lbf-in [5.08 N.m] [5.08 N.m] #12-24 Screws (not included) 2 Hole, Slotted 1/4" Stud 1/2" - 5/8" Spacing Paint Piercing Teeth Two Cable Tie Mounting Options (Cable Ties not included) Bond Sections Together using GACBJ68U, GACBJ612U, **TEBC** OR ĞACBJ618U Bond Sections Together using GACBJ68U, GACBJ612U, OR GACBJ618U Use GACBJ618U to bond ladder rack system to ground bar Use GACBJ618U to bond ladder rack

For Instructions in Local Languages and Technical Support:



system to ground bar

E-mail: cs@panduit.com

**Phone:** 800-777-3300