
Material	High Conductivity	1
Marenar	Seamless Copper Tube	
Plating	Electro-Tin	
Wire Size	2 AWG	
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric	
Wire Strip Length	1-1/4 in.	.27±.02 DIA
Stud Size	1/4 in.	.25±.04 — -
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.	<b>◄</b> .63±.04 ►
UL Temperature Rating	90° C	
C.S.A Certified Wire Connector	Yes	
Panduit Color Code on Barrel	BROWN	.10±.01 90°±5°
Panduit Die Index No. on Barrel	P33	1.16±.04
Alternate Industry Die Index No. ( ) on Barrel	(10)	
CERTIFIE	D LISTED Wire Connector	

.60±.04	2 STR CU	-Wire inspection window	
.25±.04 →		 NA	



								CORP. TINLEY PARK, ILLINOIS
								LCB2-14WF-Q
00	4/17	JHNU	JHNU	DRAWING RELEASED	019765	RGB	RGB	Copper Lug - One-Hole, Long Barrel with Window, 90° Angle Tongue
REV	DATE	BY	снк	DESCRIPTION	ECN	-R	SUP	SCALE N/A DRAWING NO / CAD FILE LCB2-14WF-CUST