THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP. GENERAL NOTES: 1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT. 16,3" 75mm 413,5mm 2. DIMENSIONS IN [] ARE METRIC.
3. ALL MATERIALS AND COMPONENTS USED MEET THE 1,6" 6,2" 40mm 157mm MATERIAL RESTRICTIONS OF ROHS (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE ROHS TECHNICAL ADAPTATION COMMITEE. 0 SPECIFIC NOTES:

5,5 bs

2,5 kg

BĭO

PANDUIT

PANDUIT A D

This tool meets requirements for Safety for Handheld Motor-Operated Electric Tools specification UL 60745-1 and CSA C22.2 No. 60745-1.

CT-3980/BT, 6.7 TON DIELESS SINGLE POINT CRIMP TOOL

Tool is listed under CSA file number 80103907. Tool meets OSHA mandated electrical and mechanical product safety requirements.

1-11-22

11-24-21

DATE

00

REVI

JHNU JHNU JADE

JEH

CHK |

APR

BJPU

BY

- 1. THE CT-3001/STBT BATTERY OPERATED TOOLS ARE DESIGNED TO CRIMP WITHOUT CRIMP DIES.
- CRIMPS PANDUIT COPPER AND ALUMINUM COMPRESSION CONNECTORS. GO TO www.panduit.com FOR MORE INFORMATION.
- 3. THIS TOOL CAN OPERATE WITH BLUE TOOTH TECHNOLOGY TO CONNECT TO THE I-PRESS PHONE APP TO MONITOR CRIMP PERFORMANCE.

THE CT-3980/BT TOOL KIT INCLUDES: QTY. DESCRIPTION/ITEM

- BATTERY OPERATED 6.7 TON HYDRAULIC TOOL
- RECHARGEABLE BATTERIES (MAKITA LI-ION 18VDC, 4Ah) MAKITA BATTERY CHARGER 120VAC (WITH

PART NUMBER

115032

093806

ECN

US PLUG CONFIGURATION) TOOL CASE

VIBR

L 75

<2,5m/s2

6 Ton

(60 kN)

<70dB

+104°F

+40°C

+14°F

-10°C

ADDED OSHA NOTE UNDER TOOL VIEW

JADE RELEASED FOR PRODUCTION

REVISED TECHNICAL INFORMATION NOTE 2: 4.9 WAS 4.6

DESCRIPTION

TECHNICAL INFORMATION:

- 1. TOOL WEIGHT (INCLUDING BATTERY) 6.0 LBS. [2.7 kg]
- 2. DIMENSIONS (INCLUDING BATTERY) 16.3" L × 4.9" H × 3.0" W $[413.5 L \times 125 H \times 75 W] mm$
- 3. CRIMPING FORCE VARIABLE 3.4 TO 6.7 TONS [34 TO 60 kN]
- 4. A COPY OF OPERATION MANUAL AND ACCESSORY INFORMATION CAN BE FOUND AT: www.panduit.com.

DIMENSIONS IN [BRACKETS] ARE IN MILLIMETERS. ALL DIMENSIONS ARE FOR REFERENCE ONLY.

> CT-3980/BT CT-3980/BT, Customer Drawing, 6.7 Ton Dieless Single, Next Generation Crimp Tool CUSTOMER DRAWING ITEM REVISION NAME 00828EBW/01 DATASET FILE NAME 00828EBW_DC/01 THIRD ANGLE PROJECTION MATERIAL AS NOTED 00828EBW_DC BJPU JEH SHEET 1 OF 1 11-24-21 NONE