



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NUMBER	WEIGHT
NKA6XPPG48Y	2.36 lb (1070.48 g)

NOTES:



1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AS WELL AS OPTIONAL ICONS.
2. MATERIAL:
PANEL HOUSING: STEEL
RJ45 MODULES: THERMOPLASTIC RESIN
UL94V-0
PUNCHDOWN BLOCKS: THERMOPLASTIC
RESIN UL94V-0
BEZEL ASSEMBLY: THERMOPLASTIC RESIN
UL94H-B
RETENTION CAP:
THERMOPLASTIC RESIN UL94V-0
3. 48 PORT ANGLED PATCH PANEL 8 POSITION
8 WIRE.
4. THE PATCH PANEL IS DESIGNED FOR
MOUNTING TO 19" UNIVERSAL RACKS.
5. FOUR (4) 12-24 X 1/2" ROUND HEAD
SCREWS ARE PROVIDED FOR FASTENING
TO RACKS.
6. DIMENSIONS IN BRACKETS ARE IN METRIC.
7. USE 110 STYLE TERMINATION
TOOL FOR PUNCHDOWN.
8. RETENTION CAPS
(ONE PER CONNECTOR)
PROVIDED FOR SNAP-IN ON TERMINATED
CONNECTORS.



PART NUMBER	PRODUCT SPEC/PKG SPEC
SEE CHART	N/A
1.1. NUMBER	WORK INSTRUCTION
N/A	N/A

NETKEY CAT6A 48 PORT ANGLED PATCH PANEL

CUSTOMER DRAWING

ITEM REVISION NAME		CUSTOMER DRAWING			
M02088AP/01					
DATASET FILE NAME		M02088AP_DC45/01A		MATERIAL: SEE NOTE 2	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] $.x \pm .1$ [2.54] $.xxx \pm .005$ [.127] $.xx \pm .01$ [.25] ANGLES $\pm 5^\circ$					
		THIRD ANGLE PROJECTION		DRAWING NUMBER: 02088-45	
DRAWN BY	DATE	CHK	SCALE	SIZE	
BJN	2-4-15	MDJR	.25:1	SHT 1 OF 1	
				A	

1	10-1-18	BAME	KRKE	MMR	A. REMOVED M6 SCREWS	M09000HW
R	2-5-15	BJN	MDJR	LPH	RELEASED TO PRODUCTION	02088-45
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN