


2

1




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NUMBER	WEIGHT	MATERIAL
FROV45SC6	0.29 LB/EACH (130g/EACH)	ABS
FROV45SC6L	0.29 LB/EACH (130g/EACH)	PC/ABS

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. THE FIBERRUNNER 6x4 OUTSIDE VERTICAL 45° ANGLE SPLIT COVER REQUIRES NO TOOLS FOR INSTALLATION AND/OR REMOVAL. THE SPLIT COVER CREATES A 3/4" (19.1) RADIUS OPENING TO ALLOW FOR NEW CABLES TO BE ADDED WITHOUT THE NEED FOR REMOVING THE COVERS.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.



B

B

A

A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
05A	9/2/2020	MES	DWR	DWR	UPDATED TITLE BLOCK, ADDED NEW PART NUMBER	V09002DZ/11

TITLE FIBERRUNNER 6x4 OUTSIDE VERTICAL 45° ANGLE SPLIT COVER (FROV45SC6, FROV45SC6L)		PANDUIT
CONTROL DRAWING		
ITEM REVISION NAME D37185EW/05		SEE PART NUMBER TABLE ABOVE
DATASET FILE NAME D37185EW/05		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .03 (.8) (.XXX) ± .005 (0.125) (.XX) ± .003 (.08) ANGLES ± .005 (0.125)		MATERIAL: SEE PART NUMBER TABLE ABOVE
DRAWING NUMBER: 37185-69		DRAWING NUMBER: 37185-69
DRAWN BY REWE	DATE 5-4-00	CHK HIW
SCALE NONE		SIZE A

2

1

D10100DA/20