



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PANDUIT P/N	WEIGHT
JOSD6TP00Y	5.69 LB/10 PCS
JOSD6TP00BL	(2583.8 g/10 PCS)

7 NOTES:


1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. BREAKOUTS DESIGNED TO ACCEPT LD3/LDP3 AND LD5/LDP5 RACEWAY.
5. KIT CONTAINS:
 - 1- BOX BASE
 - 1- BOX COVER
 - 2- PLT1.5I-M PAN-TY
 - 1- LABEL/ LABEL COVER
 - 1- COVER SCREW (USED TO SECURE COVER TO BASE)
 - 2- MAGNET (ATTACHED) (CSBM-X)
 - 6- MINI-COM TX6 PLUS JACK MODULE
 - 2- BEND RADIUS CONTROL BRIDGE
6. BASE MATERIAL THICKNESS= .090 [2.29]





BREAKOUT AREA
(3 PLACES)



LABEL HOLDER/
SECURITY SCREW
PLACEMENT



COVER REMOVED FOR CLARITY

PART NUMBER					JOSD6TP00Y, JOSD6TP00BL				
TITLE									
MINI-COM 6 POSITION SHUTTERED DEEP SURFACE MOUNT BOX KIT CUSTOMER DRAWING									
ITEM REVISION NAME									
M02479PK/00									
DATASET FILE NAME					MATERIAL: BOX: ABS DOORS: PC				
M02479PK_DC373/00C									
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .010 [.3] .XX ± .03 [.8] ANGLES ±					DRAWING NUMBER: 02479-373				
 THIRD ANGLE PROJECTION									
DRAWN BY		DATE		CHK		SCALE		SIZE	
JSP		4-25-07		MJD		NONE		SHT 1 OF 1	
								A	