HIS COPY IS PROVIDED ON Material	A RESTRICTED BASIS AND IS NOT TO BE US High Conductivity	ED IN ANY WAY DETRIMENTAI	L TO TI	HE INT	ERESTS OF PANDUIT CORP.
	Seamless Copper Tube				
Plating	Electro-Tin				.59 R Ref
Wire Size	4/0 AWG				
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric				
Wire Strip Length	1-5/8 in.	 1.06±.0	4		
Stud Size	1/2 in.				
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.	50±.04 -			.53±.02 DIA
UL Temperature Rating	90° C		-	•	3.04±.06►
C.S.A Certified Wire Connector	Yes				
Panduit Color Code on Barrel	PURPLE				
Panduit Die Index No. on Barrel	P54				Beveled wire
Alternate Industry Die Index No. () on Barrel	(15)	Wire ins	pectio	on wir	
	-	↓ [.57±.01 .71±.01	
CERTIFIE	D LISTED Wire Connector	.14±.01 —			
					CORP. TINLEY PARK, ILLINOIS
					LCB4/0-12W-X
0 6/07 JHNU JHNU	DRAWING RELEASED	021775		RGB	
EV DATE BY CHK	DESCRIPTION	ECN	-R	SUP	SCALE DRAWING NO / CAD FILE LCB4/0-12W-CUST