


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
CWMPV2340	4.55 LB/EACH PC (2063.8 g/EACH PC)

NOTES:  
 1. DIMENSIONS IN PARENTHESES ARE IN METRIC.  
 2. PART INCLUDES:  
 4- COVERS  
 1- CABLE MANAGER

MAX STORAGE TEMPERATURE 65°C (149°F)  
 MAX OPERATING TEMPERATURE 60°C (140°F)



TITLE		40 R.U. IN-CABINET VERTICAL MANAGER (FRONT ONLY) (CWMPV2340)				CUSTOMER DRAWING	
ITEM REVISION NAME		M00720AK/00				<b>PANDUIT</b>	
DATASET FILE NAME		M00720AK_DC/00C					
MATERIAL		DUCT : PVC				DRAWING NUMBER	
DRAWN BY		DATE		CHK		SCALE	
JSP		3-22-00		DPN		NONE	
REV		DATE		BY		APR	
00C		5-14-20		JBO		JEKF	
DESCRIPTION		ADDED TEMPERATURE NOTE		M09000LT		SHEET 1 OF 1	
						A	

A-SIZE CUSTOMER

2

1

2

1