

Part Number: PSCH48B

Product Description: ONE-PIECE STRUT CLAMP WITH SADDLE USED TO SECURE 2" CONDUIT



Material Specifications

Type: Zinc Plated Steel

Finish: Zinc

Color: Silver

Function Specifications

Compatible Wires and Cables

AC/MC CABLE (OD):

Drop Wire:

Plain Rod (in):

Threaded Rods and Bolts

Tapped Holes:

Clearance Holes (in):

Threaded Rod Size (in):

Compatible Conduit

EMT Size (in): 2-1/2

Rigid/IMC (in): 2-1/2

Compatible Flanges and Studs

Flange Size (in):

Metal Stud Size (ins):

Static Load Rating

Vertical (lbs): 125

Horizontal (lbs):

Other

Clamps with Saddle, suitable for use with standard 1-5/8 strut

Codes and Regulatory

Regulatory
Certifications: UL/cUL

Country of Origin: CN

Packaging

General Packaging: Cardboard Box

Box Size: 8.25 X 7.25 X 5.75

Pieces per Package: 25

Other Box Features:

Document Information

Created By: DBLA

Checked By: DJW

Approved By: KLN

Customer Specification #: C11392

Revision Level: 01

ECN #: GAECN01482

Date: 12/10/2013