



PART NUMBER	FIBER TYPE	JACKET RATING
FX8HP5NLSQMLLL	50/125 OM3	OFNP
FX8HL5NLSQMLLL		LSZH
FZ8HP5NLSQMLLL	50/125 OM4	OFNP 
FZ8HL5NLSQMLLL		LSZH

*LLL DENOTES THE LENGTH IN METERS


NOTES:

1. ALL PURCHASED ITEMS MUST CONFORM TO C2-0834 PANDUIT SPECIFICATION FOR CHEMICAL SUBSTANCES TO BE CONTROLLED IN PRODUCT AND PACKAGING.
2. ALSO AVAILABLE WITH BREAKOUT LENGTHS OF 18", 24", 36" AND 39".



MPO FIBER POSITION	FIBER COLOR	FIBER LABEL
1	BLUE	TX-1
2	ORANGE	TX-2
3	GREEN	TX-3
4	BROWN	TX-4
9	YELLOW	RX-4
10	VIOLET	RX-3
11	ROSE	RX-2
12	AQUA	RX-1

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
1	05-06-13	SAT	WMA		A. WAS "OFZH".	M02680FQ-DC
R	03-19-13	SAT	WMA		RELEASED TO PRODUCTION	M02680FQ-DC

PART NUMBER	SEE TABLE 1	PRODUCT SPEC/PKG SPEC	N/A
I.T. NUMBER	N/A	WORK INSTRUCTION	N/A
TITLE 8-FIBER MPO TO DUPLEX LC CONNECTOR MIGRATION HARNESS CUSTOMER DRAWING			
ITEM REVISION NAME	M02680FQ/00		
DATASET FILE NAME	M02680FQ_DC/00B		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.x ± .1 [2.54]	.xxx ± .005 [.127]		
.xx ± .01 [.25]	ANGLES ± 5°		
THIRD ANGLE PROJECTION	DRAWING NUMBER: M02680FQ-DC		
DRAWN BY	DATE	CHK	SCALE
SAT	03-19-13	WMA	NONE
SHT 1 OF 2			SIZE B