FiberRunner[™]24x4 LSZH Routing System EMEA




specifications

The 24x4 routing system shall be a system of channel, fittings, covers, and brackets designed to segregate, route, and protect fiber optic and high performance copper cabling. Channel and fittings shall be installed using pre-assembled couplers. Fittings maintain a minimum 3" bend radius to protect against signal loss due to excessive cable bends. Available system colours shall be yellow and black. Brackets shall be available for attaching system components to 1/2" threaded rod.



technical information

Dimensions are in inches (Dimensions in parentheses are metric)



Open channel	Cable	No. of Cables
50% fill capacity:	1.6mm	1,5820
(4" pile up)	2.0mm	1,0124
	3.0mm	4,500
Fiber Optic Ribbon		
Interconnect	5.20mm	1494
Category 6	6.35mm	1004
Category 6A	7.75mm	707
Material:	LSZH PC (Channel), LSZH PC/ABS (Fittings)	
Flammability:	94V-0	
Approvals:	UL Listed to 2024 Optical Fiber Cable Routing	
Assemblies, RoHs		Hs .
CSI Spec Form:	LP-CSISPEC-FF	R

key features and benefits

Rigid one-piece construction	Molded and extruded solid components increase the strength and integrity of the system; reduces cost of ownership and enhances network reliability	
Channel length	Solid one-piece channel is provided in 10' lengths, reducing the use of couplers and simplifying installation	
Channel covers	Snap-on channel cover is provided in four 30" lengths (totaling 10') to facilitate rapid cover installation and ease of handling	
QuikLock [™] Couplers and Brackets	No bolts need to be tightened and no tools are required when installing the QuikLock™ Couplers; ready to use right from the package; speeds installation and reduces cost	
Wide selection of directional fittings and spillouts	Offers multiple configuration options; provides design flexibility and scalability to meet wide range of applications	
Fitting covers	Channel and fitting covers protect cabling and provide fast and easy access for future cabling moves, adds, and changes	
Cable protection	A minimum 3" bend radius maintained throughout all fittings prevents excessive bends in fiber optic cabling	

applications

The FiberRunner™ 24x4 Routing System is a system of channel, fittings, covers, and brackets designed to route, manage, and protect fiber optic and high performance copper cabling above network racks and cabinets within data centers and service provider facilities. Because of its larger capacity, the 24x4 system is used to route higher cable counts. Channel and fittings are assembled using timesaving Panduit™ QuikLock™ Couplers. Fittings maintain a 3" bend radius to protect against signal loss due to excessive cable bends.

Available system colours are yellow and black to differentiate various types of cabling. The FiberRunner™ 24x4 Routing System is part of the Panduit complete fiber distribution system, which includes the FiberRunner™ 12x4, 6x4, 4x4, and 2x2 Routing Systems, Wyr-Grid™ Overhead Cable Tray System and cable management products and racks.

Channel and Cover

24x4 channel (10'): FR24X4L**10 24x4 snap-on cover (10'): FRCV24L**10

Fittings, Covers, and Sp

QuikLock™ Coupler: FRBC24X4L** Horizontal tee with 12" exits: FRT24X4W12L** Horizontal tee with 12" exits FRTCV24W12L** cover:

Horizontal 45°:

Horizontal 45° cover: FRH45CV24L** FRIV4524X4L** Inside vertical 45°. Outside vertical 45°: FROV4524X4L** Outside vertical 45° cover: FROV45CV24L** FRFWC24X4L** 4-way cross: FRFWCCV24L** 4-way cross cover:

4-way cross with 12" exits: 4-way cross with 12" exits

covér: End cap: 24" to 12" reducer: 24" to 12" reducer cover: Spill-over with 4x4 exit: Spill-over with 2x2 exit: 3-sided BRC trumpet for

FRSPJ2X2L** FRTR24X4L**

FRH4524X4L**

FRFWC24X4W12L**

FRFWCCV24W12L**

FREC24X4L**

FRRF2412L**

FRSPJ4X4L**

FRRF2412CVI **

Mounting Brackets

Trapeze bracket for new FR24TBN12 1/2" thr rod:

Trapeze bracket for existing FR24TBE12 1/2" thr rod:

Strut clip kit: **FRSTRCLIP** Two-piece ladder rack F2PCLB12

bracket for 1/2" thr rod:

*Substitute YL= Yellow, BL= Black

FiberRunner™ 24x4 Routing System EMEA


channel and cover




FR24X4L**10

FRCV24L**10

fittings, split covers, and spillouts



Mounting Brackets



**Substitute: YL = Yellow, BL = Black

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA Phone: 800.777.3300

PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575

PANDUIT JAPAN Tokyo, Japan Phone: 81.3.6863.6000

(2" bend radius)

PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000

(2" bend radius)

PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

