




PANDUIT PART NUMBER	WEIGHT
FRSSM2	0.07 LB/EACH (34g/EACH)



NOTES:

- SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
- THE FIBERRUNNER SLACK SPOOL MANAGER - 2.37" (60.3) DIAMETER IS DESIGNED WITH A MINIMUM 2" (50.8) BEND RADIUS TO PROTECT FIBER OPTIC CABLES.
- THE FIBERRUNNER SLACK SPOOL MANAGER - 2.37" (60.3) DIAMETER INCLUDES:
ONE (1) SLACK SPOOL,
ONE (1) 1/4-20x1/2 HEX HEAD CAP SCREW,
ONE (1) 1/4 SAE FLAT WASHER,
ONE (1) 1/4-20 HEX KEPS NUT
- DIMENSIONS IN PARENTHESES ARE IN METRIC.



ENG. REF.: D38419BE_DC_FRSSM2_01.prt

CAD FILENAME/LAYERS FRSSM2.pdf

PANDUIT CORP TINLEY PARK, ILLINOIS
FIBERRUNNER SLACK SPOOL MANAGER
 - 2.37" (60.3) DIAMETER (FRSSM2)
 CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ± .03 (.8) ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY MSO	MAT'L: PVC	SCALE NONE	DWG A
DATE 12-17-02	CHK'D RPA	DRAWING NO. 38419-02	SIZE A

-	-----	---	---	D. DIMENSIONED MOUNTING HOLE C. REVISED GENERAL NOTES	-----	--	--
1	7-21-06	DTP	RN	B. REVISED PART WEIGHT A. REVISED CAD FILENAME	38419-02	RN	RN
R	12-17-02	MSO	RPA	RELEASED TO PRODUCTION	38419-02	RN	RN
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST SUP GMBH