2 THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP. PANDUIT LENGTH WEIGHT WEIGHT/LENGTH PART NUMBER FRHC4L\*\*2 78.74 IN ±.36 IN 2.7 LB 0.41 LB/FT (SEE NOTE 1) (2000.0mm ±9.1mm) (1225g) (6.1g/cm) FRHC4L\*\*6 72.00 IN ±.36 IN 2.5 LB 0.41 LB/FT (SEE NOTE 1) (1828.8mm ±9.1mm) (1134g)(6.1g/cm) NOTES: 1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY. 2. DIMENSIONS IN PARENTHESES ARE IN METRIC. 5.24 -[133.0] .78 [19.7]

.10

[2.4]

В

В

2								1						
001010	REV	DATE	BY	снк	APR	DESCRIPTION	ECN	DRAWN BY	DATE 11-27-19	снк DWR	SCALE NONE	SHT 1 OF 1	A	
DA/20	00A	11-27-19	MES	DWR	DWR	RELEASED TO PRODUCTION	V09002DZ	] [		TH I PR	RD ANGLE	00485EAB-D		
								TTEM REVISION NAME 00485EAB/00 DATASET FILE NAME 00485EAB_DC/00A UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.XX) ± (.XXX) ± (.XX) ±.03 (0.8) ANGLES ±				PC		
											MATERIAL:			
											PANDUIT			
								CONTROL DRAWING						
Α								COVER (FRHC4L + + 2, FRHC4L + + 6)						
								LOW SMOKE ZERO HALOGEN FIBERRUNNER 4x4 SNAP-ON HINGED						
				_	_			TITLE						

¥.