


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
CWMPV2318	1.80 LB/EACH PC (816.5 g/EACH PC)

NOTES:

- DIMENSIONS IN PARENTHESES ARE IN METRIC.
- PART INCLUDES:
2- COVER
1- CABLE MANAGER

MAX STORAGE TEMPERATURE 65° C (149° F)
MAX OPERATING TEMPERATURE 60° C (140° F)



TITLE		18 R.U. IN-CABINET VERTICAL MANAGER (FRONT ONLY) (CWMPV2318)		
ITEM REVISION NAME		CUSTOMER DRAWING		
DATASET FILE NAME		M00720AJ/00		
MATERIAL		M00720AJ_DC/00B		
DRAWING NUMBER		00720-37		
THIRD ANGLE PROJECTION				
DRAWN BY		JSP		
DATE		3-22-00		
CHK		DPN		
SCALE		NONE		
SHEET 1 OF 1		A		

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00B	5-11-20	JBO	JCO	JEFK	ADDED TEMPERATURE NOTE	M09000LT