

<u>NOTES:</u>

PART NUMBERS: RGEJ660U, RGEJ696U, RGEJ696PF, RGEJ1024URT
DIMENSIONS IN INCHES, DIMENSIONS IN BRACKETS ARE MILLIMETERS

PANDUIT PART NUMBER	LENGTH IN [mm]
RGEJ660U	60.0 ± 1.0 [1524 ± 25]
RGEJ696U	96.0 ± 1.0 [2438 ± 25]
RGEJ660PF	60.0 ± 1.0 [1524 ± 25]
RGEJ696PF	96.0 ± 1.0 [2438 ± 25]
RGEJ1024URT	24.0 ± 1.0 [610 ± 25]

CUSTOMER DRAWING		
ITEM REVISION NAME 10J021BB/02		
10J021BB-JC_02.SLDDRW	PANDUIT	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .XX ± ANGLES ±	N/A	
THIRD ANGLE THIRD ANGLE THIRD ANGLE	DRAWING NUMBER 10J021BB-JC	
DRAWN BY DATE CHK SCALE JHNU 2/11 FLD N/A	SHEET 1 OF 1	
	STRUCTURED GROUND EQUIPMENT (RGEJ660U, RGEJ696U, RGEJ660PF, R CUSTOMER DRAWING TEM REVISION NAME 10J021BB-JC_02.SLDDRW UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .XX ± ANGLES ± THIRD ANGLE PROJECTION DRAWN BY DATE CHK SCALE	