


12 FIBER SIMPLEX SC CASSETTE - METHOD A

PART NUMBER	DESCRIPTION
FC2Z0-12-3SAS	12 FIBER 50/125um OM4 OPTIMIZED
FC2ZN-12-3SAS	12 FIBER 50/125um OM4
FC2X0-12-3SAS	12 FIBER 50/125um OM3 OPTIMIZED
FC2XN-12-3SAS	12 FIBER 50/125um OM3
FC25N-12-3SAS	12 FIBER 50/125um OM2
FC26N-12-3SAS	12 FIBER 62.5/125um OM1
FC29N-12-3SAS	12 FIBER 9/125um OS1/OS2



METHOD A - FIBER LAYOUT

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	DRAWING NUMBER	SIZE
R	10-10-12	SAT	TMSE		RELEASED TO PRODUCTION	10F113AG-DC	SAT	10-01-12	TMSE	NONE	SHT 2 OF 2	A

TITLE		12 FIBER SIMPLEX SC CASSETTE METHOD A	
ITEM REVISION NAME		10F113AG/02	
DATASET FILE NAME		10F113AG_DC/02A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		MATERIAL:	
.x ± .03 (.8)	.xxx ± .005 (.127)	SEE NOTES SHEET 1	
.xx ± .01 (.25)	ANGLES ± 5 °	DRAWING NUMBER:	
THIRD ANGLE PROJECTION		10F113AG-DC	

