

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

T.

1

1

L

I.

L

1

NOTES UNLESS OTHERWISE SPECIFIED:

PANDUIT TOOL NUMBER FCRP5 FIBER OPTIC HAND TOOL CRIMPS .048, .100, .128, .151, AND .190 HEX SIZES.

TOOL FEATURES: CUSHION HAND GRIPS CONTROLLED CYCLE REPLACEABLE DIE SET PART NUMBER = CD-FCRP5 TOOL WEIGHT = 1.20 LBS / 30.5 Kg

ADDITIONAL DIMENSIONS:

.96" (24.4 mm) MAXIMUM HANDLE WIDTH .93" (23.5 mm) MAXIMUM TOOL NOSE WIDTH

			2 1			2			SEE SHEET 1 FOR TOOL DIMENSIONS
					2 2 2				PANDUIT CORP. TINLEY PARK, ILLINDIS
	2 5								FCRP5 CUSTOMER DRAWING
	- C								UNLESSOTHERWISE SPECIFIED. UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCESADE 1.
			<u></u>						LIXELE LIXES 2 LIXES
									1.x1 1.x2xx1 1.x2xx1 2 ALL DIRPHING AS ENDING (.xx1 ANGLES IN INCLUST IN INCLUST IN INCLUST DRMM DS/JW MAT*L1 SCALE NONE
)0	9.05.01	SEI	LS	HEET 1 FOR RELATED INFO	3985		RFL	······	(.XX) ± (.XXX) ± ANGLES ± TH TROADS, THERE ARE PROJECTION

ASIZETEMP (DWG) WORK