


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. D-250A DISCONNECT ADAPTER  
COUPLES TWO FEMALE DISCONNECTS  
TO ONE MALE DISCONNECT  
ALL .250 X .032 (6.3 X 0.8)
2. MATERIAL:  
A. STAMPING: TIN PLATED BRASS
3. See [www.panduit.com](http://www.panduit.com) FOR PART NUMBER  
SUFFIX DESIGNATION FOR PACKAGE SIZE
4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
5. MAXIMUM OPERATING TEMPERATURE: 130 C°

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
08	04-26-13	JBN	RTFI	RTFI	UPDATED DRAWING BORDER & TITLE BLOCK	A41323

TITLE <b>DISCONNECT ADAPTER D-250A</b> CUSTOMER DRAWING					
ITEM REVISION NAME <b>N41323BA/07</b>			<b>PANDUIT</b>		
DATASET FILE NAME <b>N41323BA_DC/07A</b>					
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]					MATERIAL: <b>SEE NOTES</b>
.x ± .1 [ 2.54 ]		.xxx ± .005 [ .127 ]		DRAWING NUMBER: <b>A41323</b>	
.xx ± .01 [ .25 ]		ANGLES ± 5 °		THIRD ANGLE PROJECTION	
DRAWN BY <b>DAW</b>	DATE <b>-</b>	CHK <b>CJH</b>	SCALE <b>NONE</b>	SHT 1 OF 1	
					SIZE <b>A</b>

D10100DA/15