
# QuickNet™ SFQ Series MPO Fiber Adapter Panels (FAPs)

# specifications

Small Form Factor QuickNet™ (SFQ) MPO FAPs contain FOCIS 5 compatible fiber optic adapters and meet or exceed TIA/EIA-568-C.3 requirements. Variations include panels with 4, 6, or 8 MPO adapters in either key-up to key-up or key-up to key-down configurations. Maximum density allows for 64 MPO ports in a 1RU space when used in conjunction with QuickNet™ Patch Panels. All SFQ FAPs snap quickly into the rear of QuickNet™ Patch Panels for easy network deployment and quick migration.



## technical information

Standards requirements:	All adapters meet or exceed TIA/EIA-568-C.3 requirements MPO: TIA-604-5-D; FOCIS 5 compatible		
Insertion loss and Return Loss:	Supports the performance of Panduit Multimode and Singlemode MPO Patch Cords		
	Standard Multimode MPO Patch Cords:	0.50dB Max IL; 20dB Min RL	
	Optimized Multimode OM3, OM4, OM4+, OM5 MPO Patch Cords:	0.35dB Max IL; 26dB Min RL	
	Singlemode MPO APC Patch Cords:	0.75dB Max IL: 55dB Min RL	

# key features and benefits

Snap quickly into QuickNet™ Patch Panels	Assures flexibility and ease of network deployment.		
MPO adapters follow TIA/EIA-568-C.3	Type A Polarity:	Black adapter housing with key-up to key-down configuration; K=1	
and TIA-604-5-D polarity standards	Type B Polarity:	Charcoal gray adapter housing with key-up to key-up configuration; K=2	
	Type A Polarity:	Red adapter housing with key-up to key-down configuration; K=3	
MPO adapters offer a compact design for ultimate density	Fits into SC-sized simplex panel openings (See TIA/ EIA-604-3 for full dimensional details)		

# applications

The QuickNet™ SFQ Series Fiber Adapter Panels are a component of the QuickNet™ Fiber Optic Cabling System. QuickNet™ SFQ Series Fiber Adapter Panels are used in high-density network applications as specified in the Data Center Cabling Standard TIA 942 for cross connects in main distribution, horizontal distribution, and equipment distribution areas. The QuickNet™ Pre-Terminated Cabling System meets the demands of high-speed Fibre Channel

systems while maintaining compatibility with Ethernet, Fast Ethernet, and ATM. QuickNet™ SFQ Series Fiber Optic Cassettes, MPO Fiber Adapter Panels and QuickNet™ Copper Cable Assemblies are interchangeable within QuickNet™ Angled and Standard Patch Panels, enabling deployment flexibility and a unified pre-terminated solution. This ensures efficient use of space, quick deployment and the highest reliability for the lowest installed cost.

### www.panduit.com



#### QuickNet<sup>™</sup> SFQ MPO FAPs – Type A Black Adapters

FAP with 4 MPO key-up/ key-down adapters: FQMAP45BL FAP with 6 MPO key-up/ key-down adapters: FQMAP65BL FAP with 8 MPO key-up/ key-down adapters: FQMAP85BL

#### QuickNet™ SFQ MPO FAPs – Type B Charcoal Gray Adapters

FAP with 4 MPO key-up/ key-up adapters: FQMAP46CG FAP with 6 MPO key-up/ key-up adapters: FQMAP66CG FAP with 8 MPO key-up/ key-up adapters: FQMAP86CG

#### QuickNet<sup>™</sup> SFQ MPO FAPs – Type A Red (24 fiber) Adapters FAP with 4 MPO key-up/

key-up adapters: FQMAP45RD
FAP with 6 MPO key-up/
key-up adapters: FQMAP65RD
FAP with 8 MPO key-up/
key-up adapters: FQMAP85RD

#### QuickNet™ Patch Panels

 Angled 24-port:
 QAPP24BL

 Angled 48-port:
 QAPP48HDBL

 Standard 24-port:
 QPP48L

 Standard 48-port:
 QPP48HDBL


 Blanking Panel:
 QPPBBL

#### QuickNet™ Zero RU Cassette Bracket


Holds 2 cassettes: FQCBRUA

# QuickNet™ SFQ Series MPO Fiber Adapter Panels (FAPs)

# MPO Fiber Adapter Panels



Angled view of fiber adapter panel (Shown with dust caps)



Dimensions are in inches [Dimensions in brackets are metric]

#### WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA Markham, Ontario cs-cdn@panduit.com Phone: 800.777.3300

PANDUIT EUROPE LTD. London, UK cs-emea@panduit.com Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore cs-ap@panduit.com Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan cs-japan@panduit.com Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico cs-la@panduit.com Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia cs-aus@panduit.com Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com or by phone: 800.777.3300 ©2023 Panduit Corp. ALL RIGHTS RESERVED. FBSP46--WW-ENG 8/2023

