Material			High Conductivity Seamless Copper Tube							
Plating			Electro-Tin	]				/75 R REF		PANDUIT
Wire Size			750 kcmil	1 _				6		
Wire Type	)		Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric	1.89	±.04		50-12WH			
Wire Strip Length			2-15/16 in.		PA		X50 kcmil : LCB750-1			BLACK DIE P106 (24)
Stud Size			1/2 in.	]		3   {	$\times$			
UL Listed V Connecto			Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.	.63	3±.07 —			— .53±.02 DIA		Color coded barrel markings
UL Temperature Rating			90° C		Beveled wire entry					
C.S.A Cer Wire Conr	tified nector		Yes						1.03±.01	
Panduit Color Code on Barrel		de	BLACK					2.88±.07		
Panduit Die Index No. on Barrel		(No.	P106			``				
Alternate Industry Die Index No. ( ) on Barrel		/	(24)	Wire inspe	ection wind	low—			3.71 REI	=
	CER		LISTED Wire Connector	.26±.01 —				45°±5°		
									<b>CORP</b> .	TINLEY PARK, ILLINOIS
0 4/17	JHNU	IHNIII	DRAWING RELEASED		021775	RCR	RGB	Copper Lug - One-Hol	LCB750-12WH-	
	JUNUJ			,	021//0	T IN COD				