


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FIBER TYPE	PANDUIT PART NUMBER	DESCRIPTION
SINGLEMODE OS1/OS2	F1AS9N-1A12-10S	QUICKNET HIGH DENSITY CASSETTE STANDARD FIBER STRAIGHT THROUGH
	F1AS9N-1A12-10F	QUICKNET HIGH DENSITY CASSETTE STANDARD FIBER - FLIPPED PAIR
MULTIMODE OM3/OM4	F1ASXN-1A12-10S	QUICKNET HIGH DENSITY CASSETTE OM3 STANDARD FIBER STRAIGHT THROUGH
	F1ASXN-1A12-10F	QUICKNET HIGH DENSITY CASSETTE OM3 STANDARD FIBER - FLIPPED PAIR
	F1ASXO-1A12-10S	QUICKNET HIGH DENSITY CASSETTE OM3 OPTIMIZED FIBER STRAIGHT THROUGH
	F1ASXO-1A12-10F	QUICKNET HIGH DENSITY CASSETTE OM3 OPTIMIZED FIBER - FLIPPED PAIR
	F1ASZN-1A12-10S	QUICKNET HIGH DENSITY CASSETTE OM4 STANDARD FIBER STRAIGHT THROUGH
	F1ASZN-1A12-10F	QUICKNET HIGH DENSITY CASSETTE OM4 STANDARD FIBER - FLIPPED PAIR
	F1ASZO-1A12-10S	QUICKNET HIGH DENSITY CASSETTE OM4 OPTIMIZED FIBER STRAIGHT THROUGH
	F1ASZO-1A12-10F	QUICKNET HIGH DENSITY CASSETTE OM4 OPTIMIZED FIBER - FLIPPED PAIR




NOTES:

- SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
- SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
- EXCEPT FOR THE PART NUMBERS ENDING IN "F", THE HDQ CASSETTES LISTED ON THIS PRINT FOLLOW TYPE A ARRAY AS CITED IN TIA-568-C.3
- PART NUMBERS ENDING IN "F" INDICATE FLIPPED PAIRS. THE "F" OPTION REPLACES THE NEED FOR AN A-A PATCH CORD, ONLY REQUIRING TWO A-B PATCH CORDS IN THE METHOD A SYSTEM. REFERENCE TIA-568-C.0 FOR DETAILS ON METHOD A CONNECTIVITY.
- MATERIALS:
 - CASSETTE MATERIAL: ALUMINUM
 - ADAPTER: COMPOSITE PLASTIC
- ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTIONS OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
- CASSETTE WEIGHT: 49.6oz [1406g]
- DIMENSIONS IN BRACKETS ARE METRIC

1RU HDQ SERIES 144 FIBER ANGLED CASSETTE
 12 FIBER MPO TO LC WITH STANDARD LABELING
 TYPE A ARRAY FOR METHOD A CONNECTIVITY
 CUSTOMER DRAWING



PANDUIT™
 CORP.
 TINLEY PARK, ILL 60477



ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.
 DIMENSIONAL TOLERANCES ARE:
 (.X) ±.03 | (.XXX) ±.010 | (0.3) ±.010 | ANGLES

DRAWING FILENAME
 10F109AJ_DC/00B

SCALE
 NONE

DRAWN BY
 MC

REVIEW DRAWING NUMBERS

PART NO.
 SEE TABLE

DATE
 05-27-11

DRAWING NO.
 10F109AJ-DC

CHK'D
 MTV

SIZE
 A

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
01	02-07-12	EFK	MTV	RELEASED TO PRODUCTION	10F109AJ-DC	MTV	CHDE		