




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
AVPDB	2.26 LB/50 PCS (1025.1 g/50 PCS)



- NOTES:
1. SEE CURRENT CATALOG FOR PACKAGE QUANTITY.
  2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
  3. DIMENSIONS IN [ ] ARE IN METRIC.



PART NUMBER		AVPDB	
TITLE			
<b>AUDIO/VISUAL PUNCHDOWN BASE</b>		CUSTOMER DRAWING	
ITEM REVISION NAME		M00839BN/02	
DATASET FILE NAME		M00839BN_DC24/02A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]		<b>PANDUIT</b>	
.x ± .1 [ 2.54 ]      .xxx ± .005 [ .127 ] .xx ± .01 [ .25 ]      ANGLES ± 5 °			
DRAWN BY		DRAWING NUMBER: 00839-24	
DATE		SHT 1 OF 1	
CHK		SIZE A	
SCALE		THIRD ANGLE PROJECTION	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
2	3/6/14	JSP	REFR	EJH	C. UPDATED TITLE BLOCK.	00839-24
1	8/4/07	NER	DADY	KMD	B. UPDATED TITLE BLOCK. A. UPDATED MODEL TO 02.	00839-24
R	10/09/00	TA	DADY	KMD	RELEASED TO PRODUCTION	00839-24

D10100DA/14

2

1

2

1