

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



T568B WIRING SCHEME

PLUG POSITION:	CABLE WIRE:
1	WHITE/ORANGE
2	ORANGE
3	WHITE/GREEN
4	BLUE
5	WHITE/BLUE
6	GREEN
7	WHITE/BROWN
8	BROWN

PART NUMBER	LENGTH	CABLE JACKET COLOR	CABLE JACKET FLAME RATING
FC-1CCP0.5MBU	0.5m (19.7")	BLUE	PLENUM
FC-1CCP0.5MWH	0.5m (19.7")	WHITE	PLENUM
FC-1CCP1MBU	1m (39.4")	BLUE	PLENUM
FC-1CCP1MWH	1m (39.4")	WHITE	PLENUM

NOTES:

1. NOMINAL CORD JACKET DIAMETER IS .230in. (5.8mm).
2. CONSTRUCTED WITH 23AWG SOLID CAT 6A UTP CABLE.
3. TERMINATED WITH (8 POSITION) CAT 6A MODULAR PLUG AT ONE END PER T568B AND FIELD TERMINABLE SPLICE MODULE ON OTHER END.
4. TERMINATES 22-26AWG SOLID OR STRANDED UTP CABLE
5. COMPATIBLE WITH CABLE JACKET ϕ 0.189" (4.8mm) - 0.272" (6.9mm)
5. MATERIALS:
PLUG: POLYCARBONATE
SPLICE HOUSING: POLYCARBONATE
6. DIMENSIONS IN [] ARE IN METRIC.



PART NUMBER		SEE TABLE	
TITLE		TX6A™ UTP FieldCord™	
		CUSTOMER DRAWING	
ITEM REVISION NAME		00498EAA/01	
DATASET FILE NAME		00498EAA_DC/01B	
		THIRD ANGLE PROJECTION	
MATERIAL		SEE NOTES	
		DRAWING NUMBER	
		00498EAA-DC	
DRAWN BY	DATE	CHK	SCALE
BSN	2-19-21	NAGL	NONE
SHEET 1 OF 1			SIZE
			A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
01B	2-7-23	BJN	BSN	EHA	UPDATED NOMINAL CORD JACKET DIAMETER TO .230IN	00498EAA-DC

2

1

2

1

A-SIZE CUSTOMER

B

B

A

A