



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	MARKER SIZE inches [mm]	LABELS PER SHEET	SHEETS PER PKG.	STANDARD PKG. QTY.
C025X025YJJ	.25 [6.35] X .25 [6.35]	600	17	10000

NOTE:
1. MILLIMETER ARE IN [].



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
2	3/8/16	RVU	SEWH	JHAC	REMOVE REPEAT. ADD .875. REMOVE .5625.	GAECN03142
1	5/22/15	RVU	SEWH	MSAD	CHANGE FORMAT FROM B TO A. UPDATE TOLERANCES, TABLE, AND TITLE.	GAECN02364
0	9/29/04	RVU			DRAWING RELEASE.	0000

TITLE	
C025X025YJJ OPTIMUM LASER/INKJET LABELS CUSTOMER DRAWING	
ITEM REVISION NAME	100472GF/02
DATASET FILE NAME	100472GF_DC_C10238/02C
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]	MATERIAL:
.x ± .12 [3.05] .xxx ± .025 [.635]	PANDUIT GMY5
.xx ± .062 [1.57] ANGLES ±	DRAWING NUMBER:
 THIRD ANGLE PROJECTION	C10238
DRAWN BY	DATE
RVU	11/11/14
CHK	SCALE
MSAD	NTS
SHT 1 OF 1	SIZE
	A