
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



В

٧	BUNDLE DIA.		Α	В	C	D	E	F	G				WEIGHT
PANDUIT X PART NO.	MIN in (mm)	MAX in (mm)	in. (mm)	in. (mm)	in. (mm)	in. (mm)	in. (mm)	in. (mm)	in. (mm)	MIN. LOOP Ibs Tensile (n)	CROSS- SECTION	TIP STYLE	lbs/100pcs (g)
PRT2H	.188 (4.8)	2.00 (51)	.075 (1.9)	.300 (7.6)	.413 (10.5)	.300 (7.6)	.480 (12.2)	8.4 (213)	.430 (10.9)	80 (356)	HEAVY	STRAIGHT	.76 (346)
PRT3H	.188 (4.8)	3.00 (76)	.075 (1.9)	.300 (7.6)	.413 (10.5)	.300 (7.6)	.480 (12.2)	11.4 (290)	.430 (10.9)	80 (356)	HEAVY	STRAIGHT	1.04 (473)
PRT4H	.188 (4.8)	4.00 (102)	.075 (1.9)	.300 (7.6)	.413 (10.5)	.300 (7.6)	.480 (12.2)	14.5 (368)	.430 (10.9)	80 (356)	HEAVY	STRAIGHT	1.28 (581)

* SEE www.panduit.com FOR CURRENT PART NUMBER SUFFIX DESIGNATION AND FOR PACKAGE SIZE AND PART COLOR

								TITLE	1		
								PAN-TY CABLE TIES			
Α								RELEASALE SERIES			
								CUSTOMER DRAWING			
								10B0150P/02	1		
								10B0150P/02 DATASET FILE NAME 10B0150P_DC_PRT/02A			
	16	6/21/21	BWG	MPH	JADE	REMOVED PRT8H FROM DRAWING.	102299/00	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]			
	15	4/28/15	BWG	DAEI	JADE	ADDED PRT8H TO DRAWING.	SS-4472/15	.x ± .xxx ± .020 [.51] NYLON 6.6 .xx ± .02 [.5] ANGLES ±			
JA/16	14	11.17.14	BDK	MPH	JADE	UPDATED TITLE BORDER AND UPDATED NOTES	SS-4472	THIRD ANGLE PROJECTION SS-4472			
001010	REV	DATE	BY	СНК	APR	DESCRIPTION	ECN	CEW 7-31-85 HVP NONE SHT 2 OF 2			
	2					2		1	_		